

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO COMMERCIAL

Report Number: P837526

Luminaire Tested: HCSQ440D010-HM43040835-41SQMB

Issue Date: 5/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P837526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2309-165-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 5/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO COMMERCIAL
Catalog Number: HCSQ440D010-HM43040835-41SQMB
Description: HALO COMMERCIAL 4" SQUARE, NEW CONSTRUCTION FRAME, MATTE BLACK TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2024.7 lumens
Efficiency: N/A
Efficacy: 49.4 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.99
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P837526
CATALOG NUMBER: HCSQ440D010-HM43040835-41SQMB

Luminous Intensity Polar Plot





TEST NUMBER: P837526

CATALOG NUMBER: HCSQ440D010-HM43040835-41SQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93	93	93	93	93	93		
	2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87	87	87	87	87	87		
	3	102	96	91	87	100	94	90	86	92	88	84	89	86	83	87	84	82	80	80	80	80	80	80		
	4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74	74	74		
	5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69	69	69	69	69	69		
	6	87	78	72	67	85	77	71	67	76	70	67	74	70	66	73	69	66	64	64	64	64	64	64		
	7	82	73	67	63	81	72	66	62	71	66	62	70	65	62	69	65	61	60	60	60	60	60	60		
	8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56	56	56	56	56	56		
	9	74	65	58	54	73	64	58	54	63	58	54	62	57	54	61	57	54	52	52	52	52	52	52		
	10	71	61	55	51	70	60	55	51	60	54	51	59	54	51	58	54	50	49	49	49	49	49	49		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	196357	196357	196357
5°	195463	195463	195279
10°	191428	191615	191802
15°	184428	184609	184609
20°	174845	175031	175423
25°	154146	162794	153548
30°	116314	144280	117366
35°	72933	112291	75381
40°	41138	69908	41138
45°	17262	35292	17002
50°	1417	13609	1703
55°	642	2854	642
60°	736	368	736
65°	436	436	436
70°	538	538	538
75°	711	711	711
80°	0	1060	1060
85°	0	2112	2112

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 35292 cd/sqm



TEST NUMBER: P837526
 CATALOG NUMBER: HCSQ440D010-HM43040835-41SQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.0	9.4
10°-20°	516.8	25.5
20°-30°	670.4	33.1
30°-40°	476.6	23.5
40°-50°	154.5	7.6
50°-60°	11.2	0.6
60°-70°	1.9	0.1
70°-80°	2.0	0.1
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1377.2	68.0
0°-40°	1853.8	91.6
0°-60°	2019.5	99.7
0°-90°	2024.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2024.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2027	2027	2027	2027	2027	
5°	2010	2012	2010	2010	2008	190
15°	1839	1844	1841	1844	1841	516
25°	1442	1480	1523	1487	1436	646
35°	617	730	950	737	637	395
45°	126	179	258	182	124	105
55°	4	4	17	4	4	4
65°	2	2	2	2	2	2
75°	2	2	2	2	2	2
85°	0	0	2	2	2	0
90°	0	0	0	0	0	



TEST NUMBER: P837526

CATALOG NUMBER: HCSQ440D010-HM43040835-41SQMB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2026.9	2026.9	2026.9	2026.9	2026.9
2.5°	2026.9	2026.9	2025.0	2025.0	2026.9
5°	2010.0	2011.8	2010.0	2010.0	2008.1
7.5°	1987.4	1987.4	1985.5	1985.5	1985.5
10°	1946.0	1947.9	1947.9	1947.9	1949.8
12.5°	1900.9	1900.9	1900.9	1900.9	1900.9
15°	1838.9	1844.5	1840.7	1844.5	1840.7
17.5°	1776.8	1776.8	1774.9	1778.7	1774.9
20°	1696.0	1696.0	1697.8	1701.6	1701.6
22.5°	1588.8	1607.6	1615.1	1611.3	1592.5
25°	1442.1	1479.7	1523.0	1487.3	1436.5
27.5°	1257.9	1329.3	1429.0	1340.6	1261.6
30°	1039.8	1146.9	1289.8	1150.7	1049.2
32.5°	814.1	938.2	1128.1	947.6	821.7
35°	616.7	729.5	949.5	737.0	637.4
37.5°	455.0	558.4	754.0	562.2	468.2
40°	325.3	400.5	552.8	408.0	325.3
42.5°	208.7	283.9	389.2	285.8	218.1
45°	126.0	178.6	257.6	182.4	124.1
47.5°	56.4	101.5	159.8	105.3	56.4
50°	9.4	41.4	90.3	43.2	11.3
52.5°	5.6	7.5	43.2	7.5	5.6
55°	3.8	3.8	16.9	3.8	3.8
57.5°	3.8	3.8	3.8	3.8	3.8
60°	3.8	1.9	1.9	1.9	3.8
62.5°	1.9	1.9	1.9	1.9	1.9
65°	1.9	1.9	1.9	1.9	1.9
67.5°	1.9	1.9	1.9	1.9	1.9
70°	1.9	1.9	1.9	1.9	1.9
72.5°	1.9	1.9	1.9	1.9	1.9
75°	1.9	1.9	1.9	1.9	1.9
77.5°	1.9	1.9	1.9	1.9	1.9
80°	0.0	1.9	1.9	1.9	1.9
82.5°	0.0	1.9	1.9	1.9	1.9
85°	0.0	0.0	1.9	1.9	1.9
87.5°	0.0	0.0	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)