

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO COMMERCIAL

Report Number: P838296

Luminaire Tested: HCSQ607D010-HM60525827-61SQLWW

Issue Date: 5/21/2024



**Test Information**


Test Method: LM-79-2019  
Report Number: P838296  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2309-166-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 5/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO COMMERCIAL  
Catalog Number: HCSQ607D010-HM60525827-61SQLWW  
Description: HALO COMMERCIAL 6" SQUARE, NEW CONSTRUCTION FRAME, LENSED WALLWASH TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 636.3 lumens  
Efficiency: N/A  
Efficacy: 79.5 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.08 / 1.17  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P838296  
CATALOG NUMBER: HCSQ607D010-HM60525827-61SQLWW

### Luminous Intensity Polar Plot





TEST NUMBER: P838296  
 CATALOG NUMBER: HCSQ607D010-HM60525827-61SQLWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|--|--|--|--|---|
| RF  | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |    |    |    |  |  |  |  |   |
| RC  | 80  |     |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |    |    | 10 |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |  |  |  |  |   |
| 1   | 110 | 106 | 103 | 99  | 108 | 104 | 101 | 98  | 100 | 97  | 95  | 96  | 94  | 92  | 92  | 91  | 89  | 87  |    |    |    |  |  |  |  |   |
| 2   | 102 | 95  | 89  | 84  | 99  | 93  | 87  | 83  | 89  | 85  | 81  | 86  | 82  | 79  | 83  | 80  | 77  | 75  |    |    |    |  |  |  |  |   |
| 3   | 94  | 85  | 78  | 72  | 92  | 83  | 77  | 71  | 80  | 75  | 70  | 78  | 73  | 69  | 75  | 71  | 68  | 66  |    |    |    |  |  |  |  |   |
| 4   | 87  | 76  | 69  | 63  | 85  | 75  | 68  | 62  | 73  | 66  | 62  | 71  | 65  | 61  | 68  | 64  | 60  | 58  |    |    |    |  |  |  |  |   |
| 5   | 81  | 69  | 61  | 55  | 79  | 68  | 61  | 55  | 66  | 60  | 55  | 64  | 59  | 54  | 63  | 58  | 53  | 51  |    |    |    |  |  |  |  |   |
| 6   | 75  | 63  | 55  | 49  | 74  | 62  | 55  | 49  | 61  | 54  | 49  | 59  | 53  | 48  | 58  | 52  | 48  | 46  |    |    |    |  |  |  |  |   |
| 7   | 70  | 58  | 50  | 44  | 69  | 57  | 50  | 44  | 56  | 49  | 44  | 54  | 48  | 44  | 53  | 48  | 43  | 42  |    |    |    |  |  |  |  |   |
| 8   | 66  | 53  | 46  | 40  | 64  | 53  | 45  | 40  | 51  | 45  | 40  | 50  | 44  | 40  | 49  | 44  | 39  | 38  |    |    |    |  |  |  |  |   |
| 9   | 62  | 49  | 42  | 37  | 60  | 49  | 42  | 37  | 48  | 41  | 36  | 47  | 41  | 36  | 46  | 40  | 36  | 34  |    |    |    |  |  |  |  |   |
| 10  | 58  | 46  | 39  | 34  | 57  | 45  | 38  | 34  | 44  | 38  | 34  | 44  | 38  | 33  | 43  | 37  | 33  | 32  |    |    |    |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 45°   | 90°   | 135°  | 180°  |
|-----|-------|-------|-------|-------|-------|
| 0°  | 32599 | 32599 | 32599 | 32599 | 32599 |
| 5°  | 34931 | 34211 | 32548 | 30866 | 30379 |
| 10° | 36889 | 35512 | 32069 | 28881 | 27573 |
| 15° | 38232 | 36171 | 31331 | 26778 | 25073 |
| 20° | 39072 | 36469 | 30454 | 24660 | 22619 |
| 25° | 38972 | 36466 | 28764 | 22607 | 20491 |
| 30° | 35952 | 35762 | 26355 | 20672 | 18301 |
| 35° | 31446 | 33084 | 23605 | 18496 | 16569 |
| 40° | 26557 | 28631 | 20411 | 16541 | 14948 |
| 45° | 22455 | 23989 | 17468 | 14509 | 13084 |
| 50° | 19924 | 20120 | 14981 | 12645 | 11514 |
| 55° | 17836 | 17219 | 12954 | 10894 | 10826 |
| 60° | 15907 | 15016 | 11315 | 9416  | 10191 |
| 65° | 14625 | 13341 | 9834  | 8756  | 9330  |
| 70° | 13482 | 11939 | 8667  | 8157  | 8667  |
| 75° | 12689 | 10649 | 7561  | 7411  | 7973  |
| 80° | 11660 | 9568  | 6639  | 6806  | 7252  |
| 85° | 11560 | 8614  | 5558  | 5558  | 6447  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 24181 cd/sqm



TEST NUMBER: P838296

CATALOG NUMBER: HCSQ607D010-HM60525827-61SQLWW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 31.7   | 5.0       |
| 10°-20°   | 88.5   | 13.9      |
| 20°-30°   | 126.2  | 19.8      |
| 30°-40°   | 130.0  | 20.4      |
| 40°-50°   | 104.7  | 16.5      |
| 50°-60°   | 74.0   | 11.6      |
| 60°-70°   | 48.0   | 7.5       |
| 70°-80°   | 25.8   | 4.1       |
| 80°-90°   | 7.4    | 1.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 246.4  | 38.7      |
| 0°-40°    | 376.4  | 59.2      |
| 0°-60°    | 555.1  | 87.2      |
| 0°-90°    | 636.3  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 636.3  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 45° | 90° | 135° | 180° | Flux |
|-----|-----|-----|-----|------|------|------|
| 0°  | 336 | 336 | 336 | 336  | 336  |      |
| 5°  | 359 | 352 | 335 | 317  | 312  | 35   |
| 15° | 381 | 361 | 312 | 267  | 250  | 108  |
| 25° | 365 | 341 | 269 | 212  | 192  | 166  |
| 35° | 266 | 280 | 200 | 156  | 140  | 165  |
| 45° | 164 | 175 | 128 | 106  | 96   | 128  |
| 55° | 106 | 102 | 77  | 64   | 64   | 94   |
| 65° | 64  | 58  | 43  | 38   | 41   | 64   |
| 75° | 34  | 28  | 20  | 20   | 21   | 36   |
| 85° | 10  | 8   | 5   | 5    | 6    | 11   |
| 90° | 0   | 0   | 0   | 0    | 0    |      |



TEST NUMBER: P838296

CATALOG NUMBER: HCSQ607D010-HM60525827-61SQLWW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 10°   | 20°   | 30°   | 40°   | 50°   | 60°   | 70°   | 80°   | 90°   | 112.5° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 0°    | 336.5 | 336.5 | 336.5 | 336.5 | 336.5 | 336.5 | 336.5 | 336.5 | 336.5 | 336.5 | 336.5  |
| 1°    | 340.1 | 341.5 | 340.5 | 340.5 | 339.4 | 339.0 | 339.7 | 338.7 | 338.3 | 337.6 | 336.1  |
| 2°    | 346.2 | 345.1 | 344.8 | 345.1 | 343.0 | 343.0 | 341.9 | 339.7 | 338.7 | 337.2 | 333.3  |
| 3°    | 350.5 | 349.8 | 349.1 | 348.7 | 346.6 | 344.8 | 343.3 | 340.8 | 338.7 | 336.9 | 331.1  |
| 4°    | 354.5 | 354.5 | 353.8 | 352.3 | 350.2 | 348.0 | 345.1 | 342.3 | 339.0 | 335.8 | 328.2  |
| 5°    | 359.2 | 359.6 | 356.3 | 355.9 | 353.4 | 350.2 | 346.9 | 343.0 | 339.0 | 334.7 | 326.4  |
| 6°    | 363.9 | 362.1 | 361.4 | 358.8 | 355.2 | 352.3 | 348.4 | 344.1 | 338.7 | 333.6 | 322.4  |
| 7°    | 366.0 | 365.7 | 363.9 | 361.4 | 358.1 | 353.4 | 349.5 | 343.7 | 337.9 | 332.9 | 319.6  |
| 8°    | 369.6 | 369.6 | 367.5 | 364.2 | 359.6 | 355.2 | 350.2 | 343.3 | 337.6 | 331.1 | 315.6  |
| 9°    | 372.2 | 372.2 | 369.3 | 366.4 | 362.1 | 356.3 | 350.5 | 343.0 | 335.8 | 328.2 | 312.0  |
| 10°   | 375.0 | 374.3 | 372.2 | 367.8 | 364.2 | 357.8 | 350.5 | 342.6 | 334.7 | 326.0 | 308.4  |
| 11°   | 377.2 | 376.1 | 373.6 | 370.4 | 364.6 | 358.1 | 350.5 | 342.6 | 333.3 | 323.9 | 304.8  |
| 12°   | 379.0 | 378.3 | 375.0 | 371.1 | 365.3 | 358.8 | 350.2 | 341.2 | 330.7 | 321.0 | 300.1  |
| 13°   | 381.2 | 379.0 | 375.8 | 372.2 | 365.7 | 358.1 | 348.7 | 339.0 | 328.9 | 318.5 | 296.1  |
| 14°   | 380.8 | 380.4 | 377.6 | 372.5 | 365.3 | 357.4 | 348.4 | 336.9 | 326.4 | 315.6 | 291.5  |
| 15°   | 381.2 | 380.8 | 377.6 | 372.9 | 365.0 | 356.3 | 347.3 | 335.4 | 323.9 | 312.4 | 286.8  |
| 16°   | 381.2 | 381.2 | 376.8 | 372.2 | 364.6 | 355.2 | 345.1 | 334.0 | 321.4 | 309.8 | 282.8  |
| 17°   | 381.2 | 381.2 | 377.6 | 371.1 | 363.5 | 354.5 | 343.0 | 331.1 | 318.5 | 306.2 | 277.0  |
| 18°   | 381.9 | 380.8 | 376.1 | 370.7 | 362.1 | 352.7 | 341.5 | 328.9 | 316.0 | 302.3 | 273.1  |
| 19°   | 380.1 | 379.4 | 375.4 | 368.6 | 361.0 | 350.5 | 339.4 | 326.4 | 313.4 | 299.0 | 268.4  |
| 20°   | 379.0 | 380.1 | 374.7 | 367.5 | 358.8 | 348.7 | 337.2 | 323.9 | 309.8 | 295.4 | 263.7  |
| 21°   | 379.4 | 379.0 | 373.2 | 365.7 | 357.4 | 346.2 | 334.7 | 321.0 | 305.9 | 291.1 | 259.4  |
| 22.5° | 378.6 | 377.6 | 371.4 | 363.2 | 353.1 | 343.0 | 330.4 | 316.3 | 300.1 | 283.5 | 251.1  |
| 23°   | 377.2 | 376.1 | 371.4 | 362.4 | 351.6 | 341.5 | 328.2 | 313.4 | 297.9 | 281.0 | 248.9  |
| 24°   | 371.4 | 371.1 | 368.9 | 359.9 | 349.8 | 338.7 | 325.7 | 308.8 | 291.5 | 273.8 | 243.5  |
| 25°   | 364.6 | 365.3 | 364.2 | 358.5 | 346.9 | 335.4 | 321.7 | 303.0 | 285.3 | 269.1 | 237.1  |
| 26°   | 358.1 | 358.1 | 357.4 | 355.2 | 344.1 | 331.8 | 316.0 | 296.1 | 279.2 | 262.3 | 230.2  |
| 27°   | 349.8 | 351.3 | 349.8 | 348.7 | 341.2 | 327.8 | 309.8 | 291.5 | 272.4 | 255.8 | 224.4  |
| 28°   | 343.3 | 343.3 | 342.6 | 340.8 | 338.3 | 323.2 | 303.3 | 284.6 | 265.9 | 250.0 | 218.0  |
| 29°   | 331.8 | 334.0 | 334.3 | 334.7 | 334.3 | 317.0 | 297.2 | 277.0 | 259.0 | 241.7 | 211.8  |
| 30°   | 321.4 | 323.5 | 325.0 | 327.5 | 327.8 | 311.6 | 290.0 | 270.9 | 252.6 | 235.6 | 206.4  |
| 32.5° | 292.9 | 296.9 | 300.8 | 305.2 | 307.3 | 295.4 | 272.4 | 251.5 | 232.7 | 217.6 | 189.9  |
| 35°   | 265.9 | 267.0 | 271.3 | 281.4 | 283.5 | 276.0 | 251.5 | 231.7 | 214.0 | 199.6 | 174.4  |
| 37.5° | 235.3 | 237.4 | 243.5 | 255.1 | 255.8 | 249.7 | 232.7 | 209.7 | 193.1 | 180.5 | 158.5  |
| 40°   | 210.0 | 211.1 | 215.4 | 225.2 | 228.4 | 224.4 | 209.7 | 188.8 | 173.7 | 161.4 | 143.4  |
| 42.5° | 184.8 | 186.3 | 191.7 | 199.2 | 203.9 | 199.2 | 186.3 | 168.2 | 153.5 | 144.5 | 129.0  |
| 45°   | 163.9 | 165.7 | 170.8 | 175.1 | 176.5 | 173.7 | 162.1 | 147.4 | 136.9 | 127.5 | 115.6  |
| 47.5° | 145.9 | 147.7 | 151.3 | 153.1 | 154.9 | 152.0 | 143.0 | 130.8 | 120.3 | 112.8 | 102.0  |
| 50°   | 132.2 | 131.9 | 134.4 | 135.1 | 135.1 | 131.9 | 124.3 | 114.2 | 105.6 | 99.4  | 90.4   |
| 52.5° | 116.7 | 117.4 | 119.3 | 118.5 | 118.2 | 115.3 | 108.8 | 100.2 | 93.0  | 87.5  | 79.3   |
| 55°   | 105.6 | 104.5 | 105.6 | 104.8 | 103.4 | 100.5 | 94.8  | 87.5  | 81.4  | 76.7  | 69.2   |
| 57.5° | 93.3  | 93.3  | 93.7  | 92.2  | 90.4  | 87.2  | 82.1  | 76.4  | 71.0  | 67.0  | 60.9   |
| 60°   | 82.1  | 82.9  | 82.5  | 81.1  | 79.3  | 75.7  | 71.7  | 65.9  | 61.2  | 58.4  | 52.6   |



TEST NUMBER: P838296

CATALOG NUMBER: HCSQ607D010-HM60525827-61SQLWW

**CANDELA DISTRIBUTION (continued):**

|       | 0°   | 10°  | 20°  | 30°  | 40°  | 50°  | 60°  | 70°  | 80°  | 90°  | 112.5° |
|-------|------|------|------|------|------|------|------|------|------|------|--------|
| 67.5° | 55.8 | 55.8 | 54.8 | 53.7 | 51.2 | 47.9 | 45.0 | 41.4 | 38.9 | 36.4 | 32.8   |
| 70°   | 47.6 | 48.3 | 46.8 | 45.0 | 43.2 | 41.1 | 37.8 | 34.9 | 32.4 | 30.6 | 27.7   |
| 72.5° | 41.1 | 40.7 | 39.6 | 37.8 | 36.4 | 33.9 | 31.0 | 28.8 | 26.7 | 25.2 | 23.1   |
| 75°   | 33.9 | 33.9 | 32.8 | 31.3 | 29.5 | 27.4 | 25.2 | 23.4 | 21.6 | 20.2 | 19.1   |
| 77.5° | 27.0 | 27.4 | 26.3 | 25.2 | 23.8 | 21.6 | 19.8 | 18.4 | 16.9 | 15.9 | 15.1   |
| 80°   | 20.9 | 21.3 | 20.2 | 19.5 | 17.7 | 16.6 | 15.1 | 13.7 | 12.6 | 11.9 | 11.5   |
| 82.5° | 15.9 | 15.5 | 14.8 | 14.4 | 13.0 | 11.9 | 10.4 | 9.7  | 9.0  | 8.3  | 8.3    |
| 85°   | 10.4 | 10.1 | 9.7  | 9.4  | 8.3  | 7.2  | 6.8  | 6.1  | 5.4  | 5.0  | 5.0    |
| 87.5° | 5.4  | 5.4  | 5.0  | 4.7  | 4.3  | 3.6  | 3.2  | 2.5  | 2.2  | 2.2  | 2.2    |
| 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0    |



TEST NUMBER: P838296

CATALOG NUMBER: HCSQ607D010-HM60525827-61SQLWW

**CANDELA DISTRIBUTION (continued):**

|       | 135°  | 157.5° | 180°  |
|-------|-------|--------|-------|
| 0°    | 336.5 | 336.5  | 336.5 |
| 1°    | 335.1 | 333.6  | 333.3 |
| 2°    | 330.7 | 328.6  | 328.9 |
| 3°    | 326.8 | 324.2  | 321.7 |
| 4°    | 321.7 | 317.8  | 317.8 |
| 5°    | 317.4 | 313.4  | 312.4 |
| 6°    | 313.4 | 307.0  | 305.5 |
| 7°    | 309.8 | 301.9  | 299.4 |
| 8°    | 303.7 | 295.8  | 293.3 |
| 9°    | 299.4 | 290.7  | 288.2 |
| 10°   | 293.6 | 285.0  | 280.3 |
| 11°   | 288.9 | 279.2  | 275.6 |
| 12°   | 283.9 | 272.0  | 268.4 |
| 13°   | 278.1 | 265.9  | 263.7 |
| 14°   | 272.7 | 260.8  | 256.9 |
| 15°   | 267.0 | 254.7  | 250.0 |
| 16°   | 260.8 | 248.6  | 244.3 |
| 17°   | 255.8 | 242.1  | 238.9 |
| 18°   | 250.7 | 236.3  | 231.3 |
| 19°   | 244.6 | 230.9  | 225.2 |
| 20°   | 239.2 | 224.1  | 219.4 |
| 21°   | 233.5 | 219.0  | 214.0 |
| 22.5° | 225.5 | 209.3  | 204.6 |
| 23°   | 223.0 | 206.4  | 201.4 |
| 24°   | 217.2 | 200.7  | 196.3 |
| 25°   | 211.5 | 196.3  | 191.7 |
| 26°   | 206.4 | 189.9  | 185.5 |
| 27°   | 201.4 | 184.8  | 180.1 |
| 28°   | 196.0 | 179.4  | 175.8 |
| 29°   | 190.6 | 173.7  | 170.0 |
| 30°   | 184.8 | 169.7  | 163.6 |
| 32.5° | 170.4 | 156.7  | 151.7 |
| 35°   | 156.4 | 144.5  | 140.1 |
| 37.5° | 142.7 | 132.9  | 129.0 |
| 40°   | 130.8 | 122.1  | 118.2 |
| 42.5° | 118.5 | 110.6  | 106.6 |
| 45°   | 105.9 | 99.4   | 95.5  |
| 47.5° | 94.4  | 89.0   | 84.7  |
| 50°   | 83.9  | 78.5   | 76.4  |
| 52.5° | 73.9  | 70.3   | 71.3  |
| 55°   | 64.5  | 64.5   | 64.1  |
| 57.5° | 55.5  | 58.0   | 58.4  |
| 60°   | 48.6  | 51.9   | 52.6  |





TEST NUMBER: P838296

CATALOG NUMBER: HCSQ607D010-HM60525827-61SQLWW

**CANDELA DISTRIBUTION (continued):**

|       | 135° | 157.5° | 180° |
|-------|------|--------|------|
| 67.5° | 33.5 | 35.3   | 36.0 |
| 70°   | 28.8 | 30.3   | 30.6 |
| 72.5° | 24.5 | 25.6   | 26.3 |
| 75°   | 19.8 | 21.3   | 21.3 |
| 77.5° | 16.2 | 16.9   | 17.3 |
| 80°   | 12.2 | 12.6   | 13.0 |
| 82.5° | 8.6  | 9.0    | 9.4  |
| 85°   | 5.0  | 5.4    | 5.8  |
| 87.5° | 2.2  | 2.2    | 2.2  |
| 90°   | 0.0  | 0.0    | 0.0  |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





|       |      |      |      |      |      |      |      |      |      |      |      |
|-------|------|------|------|------|------|------|------|------|------|------|------|
| 62.5° | 72.8 | 73.5 | 72.4 | 70.6 | 68.8 | 65.6 | 62.0 | 56.9 | 53.3 | 50.4 | 45.4 |
| 65°   | 63.8 | 64.1 | 63.4 | 61.6 | 59.8 | 56.6 | 53.0 | 48.6 | 45.8 | 42.9 | 38.5 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



|       |      |      |      |
|-------|------|------|------|
| 62.5° | 43.6 | 46.1 | 46.5 |
| 65°   | 38.2 | 40.4 | 40.7 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)