

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585276

Luminaire Tested: **HCC8W80D010SL-HM86080930-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585276  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010SL-HM86080930-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5254.2 lumens  
Efficiency: N/A  
Efficacy: 75.1 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585276  
CATALOG NUMBER: HCC8W80D010SL-HM86080930-81NDH

### Luminous Intensity Polar Plot





TEST NUMBER: P585276

CATALOG NUMBER: HCC8W80D010SL-HM86080930-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																			
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84																			
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80																			
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75																			
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72																			
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68																			
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65																			
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62																			
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	418076
5°	354199
10°	256990
15°	192988
20°	152273
25°	122827
30°	91018
35°	36876
40°	15554
45°	8338
50°	3742
55°	1887
60°	1203
65°	854
70°	703
75°	465
80°	693
85°	1380



TEST NUMBER: P585276  
 CATALOG NUMBER: HCC8W80D010SL-HM86080930-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	982.5	18.7
10°-20°	1697.9	32.3
20°-30°	1641.6	31.2
30°-40°	721.0	13.7
40°-50°	155.8	3.0
50°-60°	35.0	0.7
60°-70°	12.0	0.2
70°-80°	4.6	0.1
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4322.0	82.3
0°-40°	5043.0	96.0
0°-60°	5233.8	99.6
0°-90°	5254.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5254.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13558	
5°	11443	982
15°	6045	1698
25°	3610	1642
35°	980	721
45°	191	156
55°	35	35
65°	12	12
75°	4	5
85°	4	4
90°	0	



TEST NUMBER: P585276  
CATALOG NUMBER: HCC8W80D010SL-HM86080930-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	13557.9
1°	13456.5
2°	13179.5
3°	12679.9
4°	12082.7
5°	11442.7
6°	10744.2
7°	10041.7
8°	9382.0
9°	8769.4
10°	8207.4
11°	7676.7
12°	7200.5
13°	6767.3
14°	6384.8
15°	6045.2
17.5°	5284.3
20°	4640.3
22.5°	4074.5
25°	3610.0
27.5°	3137.8
30°	2556.2
32.5°	1736.7
35°	979.6
37.5°	577.6
40°	386.4
42.5°	273.2
45°	191.2
47.5°	124.8
50°	78.0
52.5°	46.8
55°	35.1
57.5°	27.3
60°	19.5
62.5°	15.6
65°	11.7
67.5°	7.8
70°	7.8
72.5°	3.9
75°	3.9
77.5°	3.9
80°	3.9
82.5°	3.9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P585276  
CATALOG NUMBER: HCC8W80D010SL-HM86080930-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°	3.9
87.5°	3.9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)