

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345290

Luminaire Tested: **PR4FS12D010 PR4M12WD9FSMW 1000Lm3500K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P345290  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-4)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR4FS12D010 PR4M12WD9FSMW 1000Lm3500K  
Description: PR4 WIDE LENS WITH, MATTE WHITE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 852.2 lumens  
Efficiency: N/A  
Efficacy: 84.4 lumens/watt  
Spacing Criteria (0/90/45): 1.61 / 1.61 / 1.58  
Luminous Opening: Circular (Dia: 0.4' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P345290

CATALOG NUMBER: PR4FS12D010 PR4M12WD9FSMW 1000Lm3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P345290

CATALOG NUMBER: PR4FS12D010 PR4M12WD9FSMW 1000Lm3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62
4	84	73	64	58	82	71	63	57	69	62	57	67	61	56	64	59	55	53
5	77	65	56	50	75	64	56	50	62	55	49	60	54	49	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	44	38	65	52	44	38	51	43	38	49	43	38	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	32
9	57	44	36	31	56	44	36	31	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	21456
5°	22214
10°	24025
15°	25700
20°	27376
25°	28780
30°	29391
35°	29322
40°	28888
45°	27932
50°	26263
55°	23713
60°	20468
65°	16785
70°	13375
75°	10916
80°	9822
85°	8230



TEST NUMBER: P345290

CATALOG NUMBER: PR4FS12D010 PR4M12WD9FSMW 1000Lm3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	24.7	2.9
10°-20°	80.7	9.5
20°-30°	137.0	16.1
30°-40°	171.5	20.1
40°-50°	173.5	20.4
50°-60°	138.6	16.3
60°-70°	81.3	9.5
70°-80°	35.4	4.2
80°-90°	9.5	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.4	28.4
0°-40°	413.8	48.6
0°-60°	726.0	85.2
0°-90°	852.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	245	
5°	253	25
15°	284	81
25°	298	137
35°	275	171
45°	226	173
55°	156	139
65°	81	81
75°	32	35
85°	8	10
90°	0	



TEST NUMBER: P345290

CATALOG NUMBER: PR4FS12D010 PR4M12WD9FSMW 1000Lm3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	245.3
2.5°	247.4
5°	253.0
7.5°	261.7
10°	270.5
12.5°	278.2
15°	283.8
17.5°	289.4
20°	294.1
22.5°	297.1
25°	298.2
27.5°	296.1
30°	291.0
32.5°	283.3
35°	274.6
37.5°	264.8
40°	253.0
42.5°	240.7
45°	225.8
47.5°	209.9
50°	193.0
52.5°	174.5
55°	155.5
57.5°	136.0
60°	117.0
62.5°	98.0
65°	81.1
67.5°	65.7
70°	52.3
72.5°	41.1
75°	32.3
77.5°	25.1
80°	19.5
82.5°	13.9
85°	8.2
87.5°	3.1
90°	0.0

(END OF REPORT)