

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345360

Luminaire Tested: **PR4FS12D010 PR4M12WD8FSBZ 1000Lm4000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P345360  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-6)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR4FS12D010 PR4M12WD8FSBZ 1000Lm4000K  
Description: PR4 WIDE LENS WITH, BRONZE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 798.8 lumens  
Efficiency: N/A  
Efficacy: 76.8 lumens/watt  
Spacing Criteria (0/90/45): 1.62 / 1.62 / 1.56  
Luminous Opening: Circular (Dia: 0.4' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P345360

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1000Lm4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P345360

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1000Lm4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76
3	94	85	77	72	91	83	76	71	80	74	70	77	73	69	75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	63	59	57
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	38
8	63	51	42	37	62	50	42	37	49	41	36	47	41	36	46	40	36	34
9	59	46	38	33	58	46	38	33	45	38	33	44	37	33	43	37	32	31
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	21596
5°	22407
10°	24425
15°	26361
20°	28269
25°	29764
30°	30310
35°	30069
40°	29414
45°	28031
50°	25624
55°	22067
60°	17459
65°	12128
70°	6880
75°	2839
80°	604
85°	1204



TEST NUMBER: P345360

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1000Lm4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.0	3.1
10°-20°	82.8	10.4
20°-30°	141.6	17.7
30°-40°	175.8	22.0
40°-50°	173.6	21.7
50°-60°	128.8	16.1
60°-70°	59.5	7.4
70°-80°	10.9	1.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.4	31.2
0°-40°	425.2	53.2
0°-60°	727.5	91.1
0°-90°	798.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	798.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	247	
5°	255	25
15°	291	83
25°	308	142
35°	282	176
45°	227	174
55°	145	129
65°	59	59
75°	8	11
85°	1	1
90°	0	



TEST NUMBER: P345360

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1000Lm4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	246.9
2.5°	248.7
5°	255.2
7.5°	265.4
10°	275.0
12.5°	283.9
15°	291.1
17.5°	297.7
20°	303.7
22.5°	307.3
25°	308.4
27.5°	306.1
30°	300.1
32.5°	291.7
35°	281.6
37.5°	270.8
40°	257.6
42.5°	242.7
45°	226.6
47.5°	208.0
50°	188.3
52.5°	166.8
55°	144.7
57.5°	121.9
60°	99.8
62.5°	78.3
65°	58.6
67.5°	41.2
70°	26.9
72.5°	16.1
75°	8.4
77.5°	3.0
80°	1.2
82.5°	1.2
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)