

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585274

Luminaire Tested: **HCC8S80D010SL-HM86080930-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585274  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S80D010SL-HM86080930-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5747.1 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585274  
CATALOG NUMBER: HCC8S80D010SL-HM86080930-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P585274

CATALOG NUMBER: HCC8S80D010SL-HM86080930-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90					90			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80					80			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72					72			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65					65			
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54					54			
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50					50			
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46					46			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43					43			
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40					40			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	146950
5°	142949
10°	134516
15°	127361
20°	122506
25°	117781
30°	104605
35°	66615
40°	37179
45°	31141
50°	28107
55°	26494
60°	24176
65°	21802
70°	19240
75°	17109
80°	15165
85°	13728



TEST NUMBER: P585274  
 CATALOG NUMBER: HCC8S80D010SL-HM86080930-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	430.5	7.5
10°-20°	1125.1	19.6
20°-30°	1569.6	27.3
30°-40°	1129.4	19.7
40°-50°	559.7	9.7
50°-60°	437.9	7.6
60°-70°	296.5	5.2
70°-80°	154.0	2.7
80°-90°	44.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3125.2	54.4
0°-40°	4254.7	74.0
0°-60°	5252.3	91.4
0°-90°	5747.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5747.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4766	
5°	4618	431
15°	3990	1125
25°	3462	1570
35°	1770	1129
45°	714	560
55°	493	438
65°	299	296
75°	144	154
85°	39	44
90°	0	



TEST NUMBER: P585274

CATALOG NUMBER: HCC8S80D010SL-HM86080930-81MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4765.5
2.5°	4722.8
5°	4618.1
7.5°	4470.6
10°	4296.0
12.5°	4133.0
15°	3989.5
17.5°	3853.5
20°	3733.2
22.5°	3613.0
25°	3461.7
27.5°	3244.3
30°	2937.8
32.5°	2456.5
35°	1769.6
37.5°	1207.0
40°	923.6
42.5°	795.6
45°	714.1
47.5°	644.2
50°	585.9
52.5°	535.5
55°	492.8
57.5°	442.4
60°	392.0
62.5°	341.5
65°	298.8
67.5°	256.1
70°	213.4
72.5°	178.5
75°	143.6
77.5°	112.6
80°	85.4
82.5°	62.1
85°	38.8
87.5°	19.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)