

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345263

Luminaire Tested: **PR4FS12D010 PR4M12MD8FSBZ 2000Lm3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P345263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-3)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR4FS12D010 PR4M12MD8FSBZ 2000Lm3500K
Description: PR4 MEDIUM LENS WITH, BRONZE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1779.6 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1/1/2001
Luminous Opening: Circular (Dia: 0.4' x H: 0')
CIE Type: Direct


Input Watts (W): 19.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P345263

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSBZ 2000Lm3500K

Luminous Intensity Polar Plot





TEST NUMBER: P345263

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSBZ 2000Lm3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 100 | 98 | | 99 | 97 | 95 | | 95 | 94 | 93 | 91 |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | | 91 | 88 | 85 | | 88 | 86 | 83 | 82 |
| 3 | 98 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 86 | 82 | 78 | | 84 | 80 | 76 | | 81 | 78 | 75 | 73 |
| 4 | 92 | 83 | 76 | 71 | 90 | 82 | 76 | 71 | 79 | 74 | 70 | | 77 | 73 | 69 | | 75 | 71 | 68 | 66 |
| 5 | 86 | 76 | 69 | 64 | 85 | 75 | 69 | 64 | 73 | 68 | 63 | | 72 | 67 | 63 | | 70 | 66 | 62 | 60 |
| 6 | 81 | 70 | 63 | 58 | 79 | 70 | 63 | 58 | 68 | 62 | 58 | | 66 | 61 | 57 | | 65 | 60 | 57 | 55 |
| 7 | 76 | 65 | 58 | 53 | 75 | 65 | 58 | 53 | 63 | 57 | 53 | | 62 | 57 | 52 | | 61 | 56 | 52 | 51 |
| 8 | 72 | 61 | 54 | 49 | 70 | 60 | 53 | 49 | 59 | 53 | 49 | | 58 | 52 | 48 | | 57 | 52 | 48 | 47 |
| 9 | 68 | 57 | 50 | 45 | 67 | 56 | 50 | 45 | 55 | 49 | 45 | | 54 | 49 | 45 | | 53 | 48 | 45 | 43 |
| 10 | 64 | 53 | 46 | 42 | 63 | 53 | 46 | 42 | 52 | 46 | 42 | | 51 | 45 | 42 | | 50 | 45 | 41 | 40 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 118259 |
| 5° | 117560 |
| 10° | 115544 |
| 15° | 111627 |
| 20° | 105463 |
| 25° | 96570 |
| 30° | 84376 |
| 35° | 68051 |
| 40° | 50012 |
| 45° | 37308 |
| 50° | 28195 |
| 55° | 22006 |
| 60° | 17896 |
| 65° | 13846 |
| 70° | 10051 |
| 75° | 4867 |
| 80° | 1310 |
| 85° | 1305 |



TEST NUMBER: P345263

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSBZ 2000Lm3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 126.6 | 7.1 |
| 10°-20° | 345.3 | 19.4 |
| 20°-30° | 456.0 | 25.6 |
| 30°-40° | 394.9 | 22.2 |
| 40°-50° | 237.5 | 13.3 |
| 50°-60° | 132.4 | 7.4 |
| 60°-70° | 67.6 | 3.8 |
| 70°-80° | 17.5 | 1.0 |
| 80°-90° | 1.8 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 927.8 | 52.1 |
| 0°-40° | 1322.8 | 74.3 |
| 0°-60° | 1692.7 | 95.1 |
| 0°-90° | 1779.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1779.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1352 | |
| 5° | 1339 | 127 |
| 15° | 1233 | 345 |
| 25° | 1001 | 456 |
| 35° | 637 | 395 |
| 45° | 302 | 238 |
| 55° | 144 | 132 |
| 65° | 67 | 68 |
| 75° | 14 | 18 |
| 85° | 1 | 2 |
| 90° | 0 | |



TEST NUMBER: P345263

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSBZ 2000Lm3500K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1352.0 |
| 2.5° | 1348.1 |
| 5° | 1338.9 |
| 7.5° | 1323.2 |
| 10° | 1300.9 |
| 12.5° | 1269.4 |
| 15° | 1232.7 |
| 17.5° | 1186.8 |
| 20° | 1133.0 |
| 22.5° | 1070.1 |
| 25° | 1000.6 |
| 27.5° | 920.6 |
| 30° | 835.4 |
| 32.5° | 738.3 |
| 35° | 637.3 |
| 37.5° | 533.7 |
| 40° | 438.0 |
| 42.5° | 361.9 |
| 45° | 301.6 |
| 47.5° | 253.1 |
| 50° | 207.2 |
| 52.5° | 173.1 |
| 55° | 144.3 |
| 57.5° | 122.0 |
| 60° | 102.3 |
| 62.5° | 83.9 |
| 65° | 66.9 |
| 67.5° | 52.5 |
| 70° | 39.3 |
| 72.5° | 26.2 |
| 75° | 14.4 |
| 77.5° | 5.2 |
| 80° | 2.6 |
| 82.5° | 2.6 |
| 85° | 1.3 |
| 87.5° | 1.3 |
| 90° | 0.0 |

(END OF REPORT)