

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345227

Luminaire Tested: **PR4FS12D010 PR4M12MD8FSMMS 2000Lm3500K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P345227  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-2)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR4FS12D010 PR4M12MD8FSMMS 2000Lm3500K  
Description: PR4 MEDIUM LENS WITH, MATTE METALLIC SILVER FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2002.6 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.02  
Luminous Opening: Circular (Dia: 0.4' x H: 0')  
CIE Type: Direct


Input Watts (W): 19.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P345227

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSMMS 2000Lm3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P345227

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSMMS 2000Lm3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97		98	96	94		94	93	91	89
2	104	97	92	88	101	96	91	87	92	88	85		89	86	83		86	83	81	79
3	97	88	82	77	94	87	81	76	84	79	75		81	77	73		79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67		75	70	66		73	68	65	63
5	84	74	66	61	82	73	66	60	71	65	60		69	63	59		67	62	59	57
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62	57	53	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	44	39	61	50	43	39	49	43	39		48	43	39		47	42	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120743
5°	120054
10°	117827
15°	113964
20°	108116
25°	99697
30°	87911
35°	72226
40°	55836
45°	43617
50°	35326
55°	30393
60°	26381
65°	23326
70°	20127
75°	15952
80°	11233
85°	6624



TEST NUMBER: P345227

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSMMS 2000Lm3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.2	6.5
10°-20°	352.9	17.6
20°-30°	471.0	23.5
30°-40°	420.5	21.0
40°-50°	276.9	13.8
50°-60°	179.5	9.0
60°-70°	111.9	5.6
70°-80°	51.3	2.6
80°-90°	9.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	953.1	47.6
0°-40°	1373.6	68.6
0°-60°	1830.0	91.4
0°-90°	2002.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2002.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1380	
5°	1367	129
15°	1258	353
25°	1033	471
35°	676	420
45°	353	277
55°	199	179
65°	113	112
75°	47	51
85°	7	9
90°	0	



TEST NUMBER: P345227

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSMMS 2000Lm3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1380.4
2.5°	1377.8
5°	1367.3
7.5°	1350.2
10°	1326.6
12.5°	1296.5
15°	1258.5
17.5°	1213.9
20°	1161.5
22.5°	1099.9
25°	1033.0
27.5°	955.7
30°	870.4
32.5°	776.1
35°	676.4
37.5°	575.5
40°	489.0
42.5°	415.6
45°	352.6
47.5°	300.2
50°	259.6
52.5°	226.8
55°	199.3
57.5°	173.0
60°	150.8
62.5°	131.1
65°	112.7
67.5°	94.4
70°	78.7
72.5°	62.9
75°	47.2
77.5°	34.1
80°	22.3
82.5°	13.1
85°	6.6
87.5°	3.9
90°	0.0

(END OF REPORT)