

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585293

Luminaire Tested: **HCC8S80D010MW-HM86080935-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585293  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8S80D010MW-HM86080935-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5974.2 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585293  
CATALOG NUMBER: HCC8S80D010MW-HM86080935-81NDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585293

CATALOG NUMBER: HCC8S80D010MW-HM86080935-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95																												
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																												
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84																												
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80																												
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75																												
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72																												
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68																												
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65																												
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62																												
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	475373
5°	402741
10°	292207
15°	219437
20°	173140
25°	139659
30°	103494
35°	41932
40°	17684
45°	9485
50°	4255
55°	2150
60°	1369
65°	970
70°	802
75°	524
80°	781
85°	1557



TEST NUMBER: P585293  
 CATALOG NUMBER: HCC8S80D010MW-HM86080935-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1117.1	18.7
10°-20°	1930.6	32.3
20°-30°	1866.6	31.2
30°-40°	819.8	13.7
40°-50°	177.2	3.0
50°-60°	39.8	0.7
60°-70°	13.7	0.2
70°-80°	5.2	0.1
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4914.3	82.3
0°-40°	5734.1	96.0
0°-60°	5951.1	99.6
0°-90°	5974.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5974.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15416	
5°	13011	###
15°	6874	1931
25°	4105	1867
35°	1114	820
45°	218	177
55°	40	40
65°	13	14
75°	4	5
85°	4	4
90°	0	



TEST NUMBER: P585293  
CATALOG NUMBER: HCC8S80D010MW-HM86080935-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	15416.0
1°	15300.6
2°	14985.6
3°	14417.6
4°	13738.7
5°	13010.9
6°	12216.5
7°	11417.7
8°	10667.8
9°	9971.2
10°	9332.1
11°	8728.7
12°	8187.2
13°	7694.7
14°	7259.8
15°	6873.7
17.5°	6008.4
20°	5276.2
22.5°	4632.8
25°	4104.7
27.5°	3567.8
30°	2906.6
32.5°	1974.7
35°	1113.9
37.5°	656.8
40°	439.3
42.5°	310.7
45°	217.5
47.5°	142.0
50°	88.7
52.5°	53.3
55°	40.0
57.5°	31.0
60°	22.2
62.5°	17.7
65°	13.3
67.5°	8.9
70°	8.9
72.5°	4.4
75°	4.4
77.5°	4.4
80°	4.4
82.5°	4.4

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P585293  
CATALOG NUMBER: HCC8S80D010MW-HM86080935-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



85°	4.4
87.5°	4.4

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)