

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345269

Luminaire Tested: **PR4FS24D010 PR4M24MD8FSBZ 2000Lm3500K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P345269  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-3)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR4FS24D010 PR4M24MD8FSBZ 2000Lm3500K  
Description: PR4 MEDIUM LENS WITH, BRONZE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1779.6 lumens  
Efficiency: N/A  
Efficacy: 87.2 lumens/watt  
Spacing Criteria (0/90/45): 1/1/2001  
Luminous Opening: Circular (Dia: 0.4' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P345269

CATALOG NUMBER: PR4FS24D010 PR4M24MD8FSBZ 2000Lm3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P345269

CATALOG NUMBER: PR4FS24D010 PR4M24MD8FSBZ 2000Lm3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	76		81	78	75	73
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	85	75	69	64	73	68	63		72	67	63		70	66	62	60
6	81	70	63	58	79	70	63	58	68	62	58		66	61	57		65	60	57	55
7	76	65	58	53	75	65	58	53	63	57	53		62	57	52		61	56	52	51
8	72	61	54	49	70	60	53	49	59	53	49		58	52	48		57	52	48	47
9	68	57	50	45	67	56	50	45	55	49	45		54	49	45		53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42		51	45	42		50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	118259
5°	117560
10°	115544
15°	111627
20°	105463
25°	96570
30°	84376
35°	68051
40°	50012
45°	37308
50°	28195
55°	22006
60°	17896
65°	13846
70°	10051
75°	4867
80°	1310
85°	1305



TEST NUMBER: P345269

CATALOG NUMBER: PR4FS24D010 PR4M24MD8FSBZ 2000Lm3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.6	7.1
10°-20°	345.3	19.4
20°-30°	456.0	25.6
30°-40°	394.9	22.2
40°-50°	237.5	13.3
50°-60°	132.4	7.4
60°-70°	67.6	3.8
70°-80°	17.5	1.0
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	927.8	52.1
0°-40°	1322.8	74.3
0°-60°	1692.7	95.1
0°-90°	1779.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1779.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1352	
5°	1339	127
15°	1233	345
25°	1001	456
35°	637	395
45°	302	238
55°	144	132
65°	67	68
75°	14	18
85°	1	2
90°	0	



TEST NUMBER: P345269

CATALOG NUMBER: PR4FS24D010 PR4M24MD8FSBZ 2000Lm3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1352.0
2.5°	1348.1
5°	1338.9
7.5°	1323.2
10°	1300.9
12.5°	1269.4
15°	1232.7
17.5°	1186.8
20°	1133.0
22.5°	1070.1
25°	1000.6
27.5°	920.6
30°	835.4
32.5°	738.3
35°	637.3
37.5°	533.7
40°	438.0
42.5°	361.9
45°	301.6
47.5°	253.1
50°	207.2
52.5°	173.1
55°	144.3
57.5°	122.0
60°	102.3
62.5°	83.9
65°	66.9
67.5°	52.5
70°	39.3
72.5°	26.2
75°	14.4
77.5°	5.2
80°	2.6
82.5°	2.6
85°	1.3
87.5°	1.3
90°	0.0

(END OF REPORT)