

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585291

Luminaire Tested: **HCC8W80D010MB-HM86080935-81MDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585291  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010MB-HM86080935-81MDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6534.6 lumens  
Efficiency: N/A  
Efficacy: 93.4 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.95  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585291  
CATALOG NUMBER: HCC8W80D010MB-HM86080935-81MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P585291

CATALOG NUMBER: HCC8W80D010MB-HM86080935-81MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80	80	80	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72	72	72	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65	65	65	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59	59	59	59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54	54	54	54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50	50	50	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46	46	46	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43	43	43	43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40	40	40	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	167090
5°	162540
10°	152953
15°	144814
20°	139294
25°	133922
30°	118941
35°	75744
40°	42275
45°	35411
50°	31964
55°	30128
60°	27481
65°	24793
70°	21882
75°	19444
80°	17225
85°	15603



TEST NUMBER: P585291  
 CATALOG NUMBER: HCC8W80D010MB-HM86080935-81MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	489.5	7.5
10°-20°	1279.3	19.6
20°-30°	1784.7	27.3
30°-40°	1284.2	19.7
40°-50°	636.4	9.7
50°-60°	497.9	7.6
60°-70°	337.1	5.2
70°-80°	175.0	2.7
80°-90°	50.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3553.5	54.4
0°-40°	4837.7	74.0
0°-60°	5972.1	91.4
0°-90°	6534.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6534.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5419	
5°	5251	490
15°	4536	1279
25°	3936	1785
35°	2012	1284
45°	812	636
55°	560	498
65°	340	337
75°	163	175
85°	44	50
90°	0	



TEST NUMBER: P585291  
CATALOG NUMBER: HCC8W80D010MB-HM86080935-81MDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5418.6
2.5°	5370.1
5°	5251.0
7.5°	5083.3
10°	4884.8
12.5°	4699.4
15°	4536.2
17.5°	4381.7
20°	4244.8
22.5°	4108.1
25°	3936.1
27.5°	3688.9
30°	3340.4
32.5°	2793.2
35°	2012.1
37.5°	1372.3
40°	1050.2
42.5°	904.6
45°	812.0
47.5°	732.5
50°	666.3
52.5°	608.9
55°	560.4
57.5°	503.1
60°	445.6
62.5°	388.3
65°	339.8
67.5°	291.2
70°	242.7
72.5°	203.0
75°	163.2
77.5°	127.9
80°	97.0
82.5°	70.6
85°	44.1
87.5°	22.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)