

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585301

Luminaire Tested: **HCC8W80D010SL-HM86080935-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585301  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC8W80D010SL-HM86080935-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6777.3 lumens  
Efficiency: N/A  
Efficacy: 96.8 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 70  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585301  
CATALOG NUMBER: HCC8W80D010SL-HM86080935-81WDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P585301

CATALOG NUMBER: HCC8W80D010SL-HM86080935-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89	89	89	89	89	89	89	89	89	89	89																
	2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79	79	79	79	79	79	79	79	79	79	79																
	3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70	70	70	70	70	70	70	70	70	70	70																
	4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63	63	63	63	63	63	63	63	63	63	63																
	5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57	57	57	57	57	57	57	57	57	57	57																
	6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52	52	52	52	52	52	52	52	52	52	52																
	7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48	48	48	48	48	48	48	48	48	48	48																
	8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44	44	44	44	44	44	44	44	44	44	44																
	9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40	40	40	40	40	40	40	40	40	40	40																
	10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37	37	37	37	37	37	37	37	37	37	37																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	
0°	135492	
5°	135331	
10°	133990	
15°	132386	
20°	131160	
25°	129686	
30°	122370	
35°	99644	
40°	55051	
45°	36745	
50°	32593	
55°	30596	
60°	30195	
65°	29938	
70°	27048	
75°	24186	
80°	21150	
85°	18716	



TEST NUMBER: P585301  
 CATALOG NUMBER: HCC8W80D010SL-HM86080935-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	414.4	6.1
10°-20°	1170.9	17.3
20°-30°	1739.9	25.7
30°-40°	1566.9	23.1
40°-50°	694.6	10.2
50°-60°	514.4	7.6
60°-70°	400.0	5.9
70°-80°	216.9	3.2
80°-90°	59.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3325.1	49.1
0°-40°	4892.0	72.2
0°-60°	6101.0	90.0
0°-90°	6777.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6777.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4394	
5°	4372	414
15°	4147	1171
25°	3812	1740
35°	2647	1567
45°	843	695
55°	569	514
65°	410	400
75°	203	217
85°	53	59
90°	0	



TEST NUMBER: P585301  
CATALOG NUMBER: HCC8W80D010SL-HM86080935-81WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4393.9
2.5°	4385.2
5°	4372.0
7.5°	4336.6
10°	4279.2
12.5°	4213.1
15°	4146.9
17.5°	4080.8
20°	3996.9
22.5°	3913.1
25°	3811.6
27.5°	3657.2
30°	3436.7
32.5°	3119.0
35°	2647.0
37.5°	1976.4
40°	1367.6
42.5°	1010.3
45°	842.6
47.5°	745.5
50°	679.4
52.5°	617.6
55°	569.1
57.5°	529.3
60°	489.6
62.5°	454.4
65°	410.3
67.5°	357.3
70°	300.0
72.5°	251.5
75°	203.0
77.5°	158.9
80°	119.1
82.5°	83.8
85°	52.9
87.5°	22.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)