

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345385

Luminaire Tested: **PR4FS24D010 PR4M24WD9FSBZ 3000Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P345385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-6)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR4FS24D010 PR4M24WD9FSBZ 3000Lm3000K
Description: PR4 WIDE LENS WITH, BRONZE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1756.4 lumens
Efficiency: N/A
Efficacy: 61.6 lumens/watt
Spacing Criteria (0/90/45): 1.62 / 1.62 / 1.57
Luminous Opening: Circular (Dia: 0.4' x H: 0')
CIE Type: Direct


Input Watts (W): 28.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P345385

CATALOG NUMBER: PR4FS24D010 PR4M24WD9FSBZ 3000Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P345385

CATALOG NUMBER: PR4FS24D010 PR4M24WD9FSBZ 3000Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76
3	94	85	77	72	91	83	76	71	80	74	70	77	73	69	75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	63	59	57
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	38
8	63	51	42	37	62	50	42	37	49	41	36	47	41	36	46	40	36	34
9	59	46	38	33	58	46	38	33	45	38	33	44	37	33	43	37	32	31
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47478
5°	49275
10°	53700
15°	57964
20°	62152
25°	65454
30°	66640
35°	66108
40°	64685
45°	61615
50°	56336
55°	48510
60°	38399
65°	26658
70°	15114
75°	6218
80°	1310
85°	2609



TEST NUMBER: P345385

CATALOG NUMBER: PR4FS24D010 PR4M24WD9FSBZ 3000Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	3.1
10°-20°	182.0	10.4
20°-30°	311.2	17.7
30°-40°	386.6	22.0
40°-50°	381.6	21.7
50°-60°	283.1	16.1
60°-70°	130.7	7.4
70°-80°	23.9	1.4
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.2	31.2
0°-40°	934.9	53.2
0°-60°	1599.6	91.1
0°-90°	1756.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1756.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	543	
5°	561	55
15°	640	182
25°	678	311
35°	619	387
45°	498	382
55°	318	283
65°	129	131
75°	18	24
85°	3	2
90°	0	



TEST NUMBER: P345385

CATALOG NUMBER: PR4FS24D010 PR4M24WD9FSBZ 3000Lm3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	542.8
2.5°	546.8
5°	561.2
7.5°	583.6
10°	604.6
12.5°	624.3
15°	640.1
17.5°	654.5
20°	667.7
22.5°	675.6
25°	678.2
27.5°	672.9
30°	659.8
32.5°	641.4
35°	619.1
37.5°	595.4
40°	566.5
42.5°	533.6
45°	498.1
47.5°	457.4
50°	414.0
52.5°	366.7
55°	318.1
57.5°	268.1
60°	219.5
62.5°	172.2
65°	128.8
67.5°	90.7
70°	59.1
72.5°	35.5
75°	18.4
77.5°	6.6
80°	2.6
82.5°	2.6
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)