

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345316

Luminaire Tested: **PR4FS24D010 PR4M24WD8FSMW 4000Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P345316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-4)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR4FS24D010 PR4M24WD8FSMW 4000Lm3000K
Description: PR4 WIDE LENS WITH, MATTE WHITE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3605.5 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.61 / 1.61 / 1.58
Luminous Opening: Circular (Dia: 0.4' x H: 0')
CIE Type: Direct


Input Watts (W): 45
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P345316

CATALOG NUMBER: PR4FS24D010 PR4M24WD8FSMW 4000Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P345316

CATALOG NUMBER: PR4FS24D010 PR4M24WD8FSMW 4000Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62
4	84	73	64	58	82	71	63	57	69	62	57	67	61	56	64	59	55	53
5	77	65	56	50	75	64	56	50	62	55	49	60	54	49	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	44	38	65	52	44	38	51	43	38	49	43	38	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	32
9	57	44	36	31	56	44	36	31	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90776
5°	93985
10°	101626
15°	108729
20°	115805
25°	121750
30°	124342
35°	124036
40°	122222
45°	118171
50°	111094
55°	100329
60°	86595
65°	71012
70°	56647
75°	46232
80°	41557
85°	34825



TEST NUMBER: P345316

CATALOG NUMBER: PR4FS24D010 PR4M24WD8FSMW 4000Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.7	2.9
10°-20°	341.3	9.5
20°-30°	579.5	16.1
30°-40°	725.4	20.1
40°-50°	734.0	20.4
50°-60°	586.5	16.3
60°-70°	344.2	9.5
70°-80°	149.9	4.2
80°-90°	40.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1025.4	28.4
0°-40°	1750.8	48.6
0°-60°	3071.3	85.2
0°-90°	3605.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3605.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1038	
5°	1070	105
15°	1201	341
25°	1262	579
35°	1162	725
45°	955	734
55°	658	586
65°	343	344
75°	137	150
85°	35	40
90°	0	



TEST NUMBER: P345316

CATALOG NUMBER: PR4FS24D010 PR4M24WD8FSMW 4000Lm3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1037.8
2.5°	1046.5
5°	1070.4
7.5°	1107.3
10°	1144.2
12.5°	1176.8
15°	1200.7
17.5°	1224.6
20°	1244.1
22.5°	1257.1
25°	1261.5
27.5°	1252.8
30°	1231.1
32.5°	1198.5
35°	1161.6
37.5°	1120.4
40°	1070.4
42.5°	1018.3
45°	955.3
47.5°	888.0
50°	816.4
52.5°	738.2
55°	657.9
57.5°	575.4
60°	495.0
62.5°	414.7
65°	343.1
67.5°	277.9
70°	221.5
72.5°	173.7
75°	136.8
77.5°	106.4
80°	82.5
82.5°	58.6
85°	34.7
87.5°	13.0
90°	0.0

(END OF REPORT)