

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303347

Luminaire Tested: **PR6FS12D010 PR6M12MD8FSBZ 1000Lm3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P303347  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-3)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR6FS12D010 PR6M12MD8FSBZ 1000Lm3000K  
Description: PR6 MEDIUM LENS WITH, BRONZE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1056.0 lumens  
Efficiency: N/A  
Efficacy: 101.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P303347

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSBZ 1000Lm3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P303347

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSBZ 1000Lm3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	97	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70
4	90	80	73	67	88	78	72	67	76	70	66	74	69	65	72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58	68	62	58	66	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	51	50
7	72	61	53	48	71	60	53	47	58	52	47	57	51	47	56	51	46	45
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	36411
5°	36393
10°	36277
15°	36047
20°	35602
25°	34826
30°	33825
35°	32160
40°	29442
45°	25373
50°	20259
55°	14775
60°	9995
65°	6268
70°	3548
75°	1462
80°	0
85°	0



TEST NUMBER: P303347

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSBZ 1000Lm3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.8	5.0
10°-20°	150.3	14.2
20°-30°	222.6	21.1
30°-40°	250.8	23.8
40°-50°	210.7	20.0
50°-60°	118.6	11.2
60°-70°	42.5	4.0
70°-80°	7.6	0.7
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.7	40.3
0°-40°	676.5	64.1
0°-60°	1005.9	95.3
0°-90°	1056.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1056.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	558	
5°	556	53
15°	534	150
25°	484	223
35°	404	251
45°	275	211
55°	130	119
65°	41	43
75°	6	8
85°	0	0
90°	0	



TEST NUMBER: P303347

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSBZ 1000Lm3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	558.1
2.5°	556.9
5°	555.7
7.5°	552.3
10°	547.6
12.5°	540.7
15°	533.7
17.5°	523.3
20°	512.8
22.5°	498.9
25°	483.8
27.5°	467.6
30°	449.0
32.5°	428.1
35°	403.8
37.5°	375.9
40°	345.7
42.5°	312.1
45°	275.0
47.5°	236.7
50°	199.6
52.5°	163.6
55°	129.9
57.5°	102.1
60°	76.6
62.5°	56.9
65°	40.6
67.5°	27.8
70°	18.6
72.5°	11.6
75°	5.8
77.5°	2.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)