

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303290

Luminaire Tested: **PR6FS12D010 PR6M12MD9FSMW 1000Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12MD9FSMW 1000Lm3000K
Description: PR6 MEDIUM LENS WITH, MATTE WHITE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1038.9 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 10.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303290

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMW 1000Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P303290

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMW 1000Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	40	36	35
10	58	46	39	34	57	46	38	34	45	38	34	44	38	33	43	37	33	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33488
5°	33419
10°	33276
15°	32906
20°	32506
25°	31969
30°	31188
35°	29859
40°	27662
45°	24238
50°	19843
55°	15503
60°	11639
65°	8815
70°	7077
75°	6075
80°	5260
85°	3743



TEST NUMBER: P303290

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMW 1000Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	4.7
10°-20°	137.4	13.2
20°-30°	204.5	19.7
30°-40°	233.3	22.5
40°-50°	201.2	19.4
50°-60°	123.2	11.9
60°-70°	58.6	5.6
70°-80°	26.0	2.5
80°-90°	6.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	390.4	37.6
0°-40°	623.6	60.0
0°-60°	948.0	91.2
0°-90°	1038.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1038.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	513	
5°	510	48
15°	487	137
25°	444	204
35°	375	233
45°	263	201
55°	136	123
65°	57	59
75°	24	26
85°	5	6
90°	0	



TEST NUMBER: P303290

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMW 1000Lm3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	513.3
2.5°	512.3
5°	510.3
7.5°	507.3
10°	502.3
12.5°	495.3
15°	487.2
17.5°	478.2
20°	468.2
22.5°	457.2
25°	444.1
27.5°	431.1
30°	414.0
32.5°	396.0
35°	374.9
37.5°	351.9
40°	324.8
42.5°	294.7
45°	262.7
47.5°	228.6
50°	195.5
52.5°	164.4
55°	136.3
57.5°	110.3
60°	89.2
62.5°	71.2
65°	57.1
67.5°	46.1
70°	37.1
72.5°	30.1
75°	24.1
77.5°	19.0
80°	14.0
82.5°	10.0
85°	5.0
87.5°	1.0
90°	0.0

(END OF REPORT)