

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P434589

Luminaire Tested: **HCM1R25940ED010MW**

Issue Date: 11/24/2020

Test Information

Test Method: LM-41-14
Report Number: P434589
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-933-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/24/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCM1R25940ED010MW
Description: HALO COMMERCIAL 4INCH ADJUSTABLE MULTIPLE, 25 DEG REFLECTOR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1313.6 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434589

CATALOG NUMBER: HCM1R25940ED010MW

Luminous Intensity Polar Plot





TEST NUMBER: P434589

CATALOG NUMBER: HCM1R25940ED010MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | | |
| 2 | 109 | 104 | 100 | 97 | 107 | 102 | 99 | 96 | 99 | 96 | 94 | 96 | 94 | 92 | 94 | 92 | 90 | 88 | | |
| 3 | 104 | 98 | 93 | 90 | 102 | 97 | 92 | 89 | 94 | 91 | 88 | 92 | 89 | 86 | 89 | 87 | 85 | 83 | | |
| 4 | 100 | 93 | 88 | 84 | 98 | 92 | 87 | 83 | 89 | 85 | 82 | 88 | 84 | 81 | 86 | 83 | 80 | 79 | | |
| 5 | 95 | 88 | 83 | 79 | 94 | 87 | 82 | 78 | 85 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 75 | | |
| 6 | 92 | 84 | 78 | 75 | 90 | 83 | 78 | 74 | 81 | 77 | 74 | 80 | 76 | 73 | 79 | 76 | 73 | 72 | | |
| 7 | 88 | 80 | 75 | 71 | 87 | 79 | 74 | 71 | 78 | 74 | 70 | 77 | 73 | 70 | 76 | 72 | 70 | 68 | | |
| 8 | 85 | 76 | 71 | 68 | 84 | 76 | 71 | 67 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 69 | 67 | 65 | | |
| 9 | 82 | 73 | 68 | 65 | 81 | 73 | 68 | 65 | 72 | 68 | 64 | 71 | 67 | 64 | 70 | 67 | 64 | 63 | | |
| 10 | 79 | 70 | 65 | 62 | 78 | 70 | 65 | 62 | 69 | 65 | 62 | 69 | 65 | 62 | 68 | 64 | 62 | 60 | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2252820 |
| 5° | 2016320 |
| 10° | 1372664 |
| 15° | 709479 |
| 20° | 370103 |
| 25° | 297070 |
| 30° | 281947 |
| 35° | 219540 |
| 40° | 75806 |
| 45° | 33003 |
| 50° | 28323 |
| 55° | 24773 |
| 60° | 21610 |
| 65° | 20197 |
| 70° | 21638 |
| 75° | 26307 |
| 80° | 32674 |
| 85° | 6793 |



TEST NUMBER: P434589

CATALOG NUMBER: HCM1R25940ED010MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 344.8 | 26.2 |
| 10°-20° | 396.3 | 30.2 |
| 20°-30° | 258.8 | 19.7 |
| 30°-40° | 209.4 | 15.9 |
| 40°-50° | 42.5 | 3.2 |
| 50°-60° | 25.6 | 1.9 |
| 60°-70° | 17.7 | 1.3 |
| 70°-80° | 14.8 | 1.1 |
| 80°-90° | 3.8 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 999.9 | 76.1 |
| 0°-40° | 1209.3 | 92.1 |
| 0°-60° | 1277.3 | 97.2 |
| 0°-90° | 1313.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1313.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4566 | |
| 5° | 4071 | 345 |
| 15° | 1389 | 396 |
| 25° | 546 | 259 |
| 35° | 364 | 209 |
| 45° | 47 | 42 |
| 55° | 29 | 26 |
| 65° | 17 | 18 |
| 75° | 14 | 15 |
| 85° | 1 | 4 |
| 90° | 0 | |



TEST NUMBER: P434589

CATALOG NUMBER: HCM1R25940ED010MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 4566.1 |
| 1° | 4525.7 |
| 2° | 4443.8 |
| 3° | 4341.1 |
| 4° | 4222.3 |
| 5° | 4071.2 |
| 6° | 3875.0 |
| 7° | 3627.0 |
| 8° | 3337.5 |
| 9° | 3042.1 |
| 10° | 2739.9 |
| 11° | 2438.8 |
| 12° | 2150.4 |
| 13° | 1874.7 |
| 14° | 1622.0 |
| 15° | 1389.0 |
| 16° | 1199.8 |
| 17° | 1025.6 |
| 18° | 889.4 |
| 19° | 783.3 |
| 20° | 704.9 |
| 22.5° | 595.3 |
| 25° | 545.7 |
| 26° | 533.0 |
| 27° | 523.7 |
| 28° | 514.5 |
| 29° | 504.1 |
| 30° | 494.9 |
| 32.5° | 460.3 |
| 35° | 364.5 |
| 37.5° | 234.2 |
| 40° | 117.7 |
| 42.5° | 56.5 |
| 45° | 47.3 |
| 47.5° | 41.5 |
| 50° | 36.9 |
| 52.5° | 32.3 |
| 55° | 28.8 |
| 57.5° | 24.2 |
| 60° | 21.9 |
| 62.5° | 19.6 |
| 65° | 17.3 |
| 67.5° | 16.2 |



TEST NUMBER: P434589

CATALOG NUMBER: HCM1R25940ED010MW

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 75° | 13.8 |
| 77.5° | 13.8 |
| 80° | 11.5 |
| 82.5° | 6.9 |
| 85° | 1.2 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|------|
| 70° | | 15.0 |
| 72.5° | | 15.0 |



(END OF REPORT)