

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303439

Luminaire Tested: **PR6FS12D010 PR6M12WD8FSBZ 1000Lm4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303439
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-6)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12WD8FSBZ 1000Lm4000K
Description: PR6 WIDE LENS WITH, BRONZE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1139.8 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.26
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 10.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303439

CATALOG NUMBER: PR6FS12D010 PR6M12WD8FSBZ 1000Lm4000K

Luminous Intensity Polar Plot





TEST NUMBER: P303439

CATALOG NUMBER: PR6FS12D010 PR6M12WD8FSBZ 1000Lm4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85		90	86	83		87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75		82	77	74		79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66		75	70	66		73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		67	62	58	56
6	78	67	59	54	76	66	59	53	64	58	53		63	57	53		61	56	52	50
7	73	61	54	48	71	61	53	48	59	53	48		58	52	48		56	51	47	46
8	68	56	49	44	67	56	49	44	55	48	43		53	48	43		52	47	43	41
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36		46	40	36		45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36861
5°	37663
10°	38774
15°	39613
20°	40108
25°	40218
30°	39422
35°	36644
40°	31758
45°	25188
50°	18736
55°	13797
60°	10060
65°	6823
70°	4349
75°	1916
80°	488
85°	0



TEST NUMBER: P303439

CATALOG NUMBER: PR6FS12D010 PR6M12WD8FSBZ 1000Lm4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.2	4.8
10°-20°	165.7	14.5
20°-30°	256.5	22.5
30°-40°	284.5	25.0
40°-50°	211.0	18.5
50°-60°	110.9	9.7
60°-70°	45.9	4.0
70°-80°	9.8	0.9
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.4	41.9
0°-40°	761.9	66.8
0°-60°	1083.9	95.1
0°-90°	1139.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1139.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	565	
5°	575	55
15°	586	166
25°	559	256
35°	460	284
45°	273	211
55°	121	111
65°	44	46
75°	8	10
85°	0	0
90°	0	



TEST NUMBER: P303439

CATALOG NUMBER: PR6FS12D010 PR6M12WD8FSBZ 1000Lm4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	565.0
2.5°	568.8
5°	575.1
7.5°	581.5
10°	585.3
12.5°	587.8
15°	586.5
17.5°	584.0
20°	577.7
22.5°	570.1
25°	558.7
27.5°	543.5
30°	523.3
32.5°	496.8
35°	460.1
37.5°	418.4
40°	372.9
42.5°	322.3
45°	273.0
47.5°	226.3
50°	184.6
52.5°	149.2
55°	121.3
57.5°	97.3
60°	77.1
62.5°	59.4
65°	44.2
67.5°	32.9
70°	22.8
72.5°	15.2
75°	7.6
77.5°	2.5
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)