

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303446

Luminaire Tested: **PR6FS12D010 PR6M12WD9FSBZ 1500Lm3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P303446  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-6)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR6FS12D010 PR6M12WD9FSBZ 1500Lm3000K  
Description: PR6 WIDE LENS WITH, BRONZE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1157.9 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.26  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P303446

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSBZ 1500Lm3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P303446

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSBZ 1500Lm3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50
7	73	61	54	48	71	61	53	48	59	53	48	58	52	48	56	51	47	46
8	68	56	49	44	67	56	49	44	55	48	43	53	48	43	52	47	43	41
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	37448
5°	38266
10°	39391
15°	40248
20°	40747
25°	40859
30°	40047
35°	37226
40°	32261
45°	25594
50°	19031
55°	14025
60°	10217
65°	6931
70°	4406
75°	1941
80°	488
85°	0



TEST NUMBER: P303446

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSBZ 1500Lm3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.1	4.8
10°-20°	168.3	14.5
20°-30°	260.6	22.5
30°-40°	289.0	25.0
40°-50°	214.4	18.5
50°-60°	112.7	9.7
60°-70°	46.7	4.0
70°-80°	9.9	0.9
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	485.0	41.9
0°-40°	774.0	66.8
0°-60°	1101.2	95.1
0°-90°	1157.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1157.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	574	
5°	584	56
15°	596	168
25°	568	261
35°	467	289
45°	277	214
55°	123	113
65°	45	47
75°	8	10
85°	0	0
90°	0	



TEST NUMBER: P303446

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSBZ 1500Lm3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	574.0
2.5°	577.9
5°	584.3
7.5°	590.7
10°	594.6
12.5°	597.1
15°	595.9
17.5°	593.3
20°	586.9
22.5°	579.2
25°	567.6
27.5°	552.2
30°	531.6
32.5°	504.7
35°	467.4
37.5°	425.1
40°	378.8
42.5°	327.5
45°	277.4
47.5°	229.9
50°	187.5
52.5°	151.5
55°	123.3
57.5°	98.9
60°	78.3
62.5°	60.4
65°	44.9
67.5°	33.4
70°	23.1
72.5°	15.4
75°	7.7
77.5°	2.6
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)