

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303617

Luminaire Tested: **PR6FS12D010 PR6M12MD9FSMMS 2000Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3000K
Description: PR6 MEDIUM LENS WITH, MATTE METALLIC SILVER FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1939.3 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303617

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P303617

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	96	87	81	75	94	86	80	75	83	78	74	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	45	41	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65025
5°	65012
10°	64704
15°	64205
20°	63492
25°	62368
30°	60884
35°	57822
40°	53458
45°	46446
50°	37452
55°	28288
60°	19885
65°	13307
70°	8412
75°	5067
80°	3006
85°	1497



TEST NUMBER: P303617

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	4.9
10°-20°	268.1	13.8
20°-30°	398.8	20.6
30°-40°	452.3	23.3
40°-50°	384.9	19.8
50°-60°	225.3	11.6
60°-70°	89.4	4.6
70°-80°	23.7	1.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	761.0	39.2
0°-40°	1213.3	62.6
0°-60°	1823.5	94.0
0°-90°	1939.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1939.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	997	
5°	993	94
15°	951	268
25°	866	399
35°	726	452
45°	503	385
55°	249	225
65°	86	89
75°	20	24
85°	2	3
90°	0	



TEST NUMBER: P303617

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	996.7
2.5°	994.7
5°	992.7
7.5°	984.7
10°	976.7
12.5°	964.6
15°	950.6
17.5°	934.6
20°	914.5
22.5°	892.5
25°	866.4
27.5°	838.3
30°	808.2
32.5°	770.1
35°	726.0
37.5°	679.9
40°	627.7
42.5°	567.6
45°	503.4
47.5°	433.2
50°	369.0
52.5°	306.8
55°	248.7
57.5°	196.5
60°	152.4
62.5°	116.3
65°	86.2
67.5°	62.2
70°	44.1
72.5°	32.1
75°	20.1
77.5°	12.0
80°	8.0
82.5°	4.0
85°	2.0
87.5°	0.0
90°	0.0

(END OF REPORT)