

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303360

Luminaire Tested: **PR6FS24D010 PR6M24MD8FSBZ 2000Lm3500K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P303360  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-3)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR6FS24D010 PR6M24MD8FSBZ 2000Lm3500K  
Description: PR6 MEDIUM LENS WITH, BRONZE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2376.4 lumens  
Efficiency: N/A  
Efficacy: 116.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P303360

CATALOG NUMBER: PR6FS24D010 PR6M24MD8FSBZ 2000Lm3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P303360

CATALOG NUMBER: PR6FS24D010 PR6M24MD8FSBZ 2000Lm3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86	84	81	79
3	97	88	82	76	94	87	81	76	84	79	74		81	77	73		79	75	72	70
4	90	80	73	67	88	78	72	67	76	70	66		74	69	65		72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58		68	62	58		66	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		61	55	51	50
7	72	61	53	48	71	60	53	47	58	52	47		57	51	47		56	51	46	45
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36		45	40	35		45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	81936
5°	81908
10°	81643
15°	81118
20°	80119
25°	78377
30°	76117
35°	72365
40°	66267
45°	57093
50°	45582
55°	33259
60°	22482
65°	14110
70°	7973
75°	3302
80°	0
85°	0



TEST NUMBER: P303360

CATALOG NUMBER: PR6FS24D010 PR6M24MD8FSBZ 2000Lm3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.8	5.0
10°-20°	338.2	14.2
20°-30°	501.0	21.1
30°-40°	564.4	23.8
40°-50°	474.2	20.0
50°-60°	267.0	11.2
60°-70°	95.7	4.0
70°-80°	17.1	0.7
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	957.9	40.3
0°-40°	1522.4	64.1
0°-60°	2263.6	95.3
0°-90°	2376.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2376.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1256	
5°	1251	119
15°	1201	338
25°	1089	501
35°	909	564
45°	619	474
55°	292	267
65°	91	96
75°	13	17
85°	0	0
90°	0	



TEST NUMBER: P303360

CATALOG NUMBER: PR6FS24D010 PR6M24MD8FSBZ 2000Lm3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1255.9
2.5°	1253.3
5°	1250.7
7.5°	1242.8
10°	1232.4
12.5°	1216.7
15°	1201.0
17.5°	1177.5
20°	1154.0
22.5°	1122.7
25°	1088.8
27.5°	1052.2
30°	1010.4
32.5°	963.4
35°	908.6
37.5°	846.0
40°	778.1
42.5°	702.4
45°	618.8
47.5°	532.6
50°	449.1
52.5°	368.1
55°	292.4
57.5°	229.8
60°	172.3
62.5°	127.9
65°	91.4
67.5°	62.7
70°	41.8
72.5°	26.1
75°	13.1
77.5°	5.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)