

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P434645

Luminaire Tested: **HCM3R15935ED010MMS**

Issue Date: 11/24/2020

Test Information

Test Method: LM-41-14
Report Number: P434645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-933-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/24/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCM3R15935ED010MMS
Description: HALO COMMERCIAL 4INCH ADJUSTABLE MULTIPLE, 15 DEG REFLECTOR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3853.6 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.25
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434645

CATALOG NUMBER: HCM3R15935ED010MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434645

CATALOG NUMBER: HCM3R15935ED010MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89		
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85		
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77		
6	93	86	81	77	92	85	80	77	83	79	76	82	79	76	81	78	75	74		
7	90	82	77	74	89	82	77	73	80	76	73	79	75	73	78	75	72	71		
8	87	79	74	71	86	78	74	70	77	73	70	77	73	70	76	72	70	68		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66		
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12482848
5°	9235389
10°	3482938
15°	1431728
20°	960567
25°	835140
30°	808982
35°	630794
40°	211896
45°	103057
50°	90189
55°	63567
60°	56344
65°	54869
70°	58135
75°	76823
80°	95466
85°	19247



TEST NUMBER: P434645

CATALOG NUMBER: HCM3R15935ED010MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1373.4	35.6
10°-20°	863.8	22.4
20°-30°	719.3	18.7
30°-40°	600.5	15.6
40°-50°	127.5	3.3
50°-60°	70.3	1.8
60°-70°	47.0	1.2
70°-80°	40.8	1.1
80°-90°	10.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2956.5	76.7
0°-40°	3557.0	92.3
0°-60°	3754.8	97.4
0°-90°	3853.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3853.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25301	
5°	18647	###
15°	2803	864
25°	1534	719
35°	1047	601
45°	148	127
55°	74	70
65°	47	47
75°	40	41
85°	3	11
90°	0	



TEST NUMBER: P434645

CATALOG NUMBER: HCM3R15935ED010MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	25300.7
1°	24995.3
2°	24253.4
3°	22927.4
4°	20997.2
5°	18647.4
6°	16133.1
7°	13575.2
8°	11074.3
9°	8862.1
10°	6952.1
11°	5481.8
12°	4441.1
13°	3712.7
14°	3192.4
15°	2803.0
16°	2504.2
17°	2272.6
18°	2091.3
19°	1950.3
20°	1829.5
22.5°	1624.7
25°	1534.1
26°	1507.2
27°	1487.1
28°	1467.0
29°	1443.5
30°	1420.0
32.5°	1326.0
35°	1047.3
37.5°	668.0
40°	329.0
42.5°	157.8
45°	147.7
47.5°	137.6
50°	117.5
52.5°	90.6
55°	73.9
57.5°	63.8
60°	57.1
62.5°	50.4
65°	47.0
67.5°	43.6



TEST NUMBER: P434645

CATALOG NUMBER: HCM3R15935ED010MMS

CANDELA DISTRIBUTION (continued):

	0°
75°	40.3
77.5°	36.9
80°	33.6
82.5°	20.1
85°	3.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	40.3
72.5°	40.3



(END OF REPORT)