

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303618

Luminaire Tested: **PR6FS12D010 PR6M12MD9FSMMS 2000Lm3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303618
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3500K
Description: PR6 MEDIUM LENS WITH, MATTE METALLIC SILVER FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2100.9 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303618

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3500K

Luminous Intensity Polar Plot





TEST NUMBER: P303618

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	96	87	81	75	94	86	80	75	83	78	74	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	45	41	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70447
5°	70428
10°	70089
15°	69555
20°	68782
25°	67565
30°	65962
35°	62640
40°	57913
45°	50312
50°	40578
55°	30643
60°	21542
65°	14418
70°	9118
75°	5470
80°	3269
85°	1647



TEST NUMBER: P303618

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	4.9
10°-20°	290.4	13.8
20°-30°	432.0	20.6
30°-40°	490.0	23.3
40°-50°	417.0	19.8
50°-60°	244.1	11.6
60°-70°	96.8	4.6
70°-80°	25.7	1.2
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	824.4	39.2
0°-40°	1314.4	62.6
0°-60°	1975.4	94.0
0°-90°	2100.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2100.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1080	
5°	1075	102
15°	1030	290
25°	939	432
35°	786	490
45°	545	417
55°	269	244
65°	93	97
75°	22	26
85°	2	3
90°	0	



TEST NUMBER: P303618

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 2000Lm3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1079.8
2.5°	1077.6
5°	1075.4
7.5°	1066.7
10°	1058.0
12.5°	1045.0
15°	1029.8
17.5°	1012.4
20°	990.7
22.5°	966.8
25°	938.6
27.5°	908.1
30°	875.6
32.5°	834.3
35°	786.5
37.5°	736.5
40°	680.0
42.5°	614.8
45°	545.3
47.5°	469.3
50°	399.8
52.5°	332.4
55°	269.4
57.5°	212.9
60°	165.1
62.5°	126.0
65°	93.4
67.5°	67.4
70°	47.8
72.5°	34.8
75°	21.7
77.5°	13.0
80°	8.7
82.5°	4.3
85°	2.2
87.5°	0.0
90°	0.0

(END OF REPORT)