

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345250

Luminaire Tested: **PR4FS12D010 PR4M12MD8FSBZ 1000Lm3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P345250  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-3)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR4FS12D010 PR4M12MD8FSBZ 1000Lm3000K  
Description: PR4 MEDIUM LENS WITH, BRONZE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 763.9 lumens  
Efficiency: N/A  
Efficacy: 73.5 lumens/watt  
Spacing Criteria (0/90/45): 1/1/2001  
Luminous Opening: Circular (Dia: 0.4' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P345250

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSBZ 1000Lm3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P345250

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSBZ 1000Lm3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	76	81	78	75	73
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	85	75	69	64	73	68	63	72	67	63	70	66	62	60
6	81	70	63	58	79	70	63	58	68	62	58	66	61	57	65	60	57	55
7	76	65	58	53	75	65	58	53	63	57	53	62	57	52	61	56	52	51
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	50767
5°	50461
10°	49596
15°	47913
20°	45266
25°	41452
30°	36219
35°	29215
40°	21466
45°	16019
50°	12097
55°	9440
60°	7680
65°	5940
70°	4322
75°	2095
80°	554
85°	602



TEST NUMBER: P345250

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSBZ 1000Lm3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.3	7.1
10°-20°	148.2	19.4
20°-30°	195.7	25.6
30°-40°	169.5	22.2
40°-50°	102.0	13.3
50°-60°	56.8	7.4
60°-70°	29.0	3.8
70°-80°	7.6	1.0
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	398.3	52.1
0°-40°	567.8	74.3
0°-60°	726.6	95.1
0°-90°	763.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	763.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	580	
5°	575	54
15°	529	148
25°	430	196
35°	274	170
45°	130	102
55°	62	57
65°	29	29
75°	6	8
85°	1	1
90°	0	



TEST NUMBER: P345250

CATALOG NUMBER: PR4FS12D010 PR4M12MD8FSBZ 1000Lm3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	580.4
2.5°	578.7
5°	574.7
7.5°	568.0
10°	558.4
12.5°	544.9
15°	529.1
17.5°	509.4
20°	486.3
22.5°	459.3
25°	429.5
27.5°	395.2
30°	358.6
32.5°	316.9
35°	273.6
37.5°	229.1
40°	188.0
42.5°	155.4
45°	129.5
47.5°	108.6
50°	88.9
52.5°	74.3
55°	61.9
57.5°	52.3
60°	43.9
62.5°	36.0
65°	28.7
67.5°	22.5
70°	16.9
72.5°	11.3
75°	6.2
77.5°	2.3
80°	1.1
82.5°	1.1
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)