

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303607

Luminaire Tested: **PR6FS12D010 PR6M12MD8FSBZ 2000Lm4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303607
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-3)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12MD8FSBZ 2000Lm4000K
Description: PR6 MEDIUM LENS WITH, BRONZE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2257.4 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303607

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSBZ 2000Lm4000K

Luminous Intensity Polar Plot





TEST NUMBER: P303607

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSBZ 2000Lm4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86	84	81	79
3	97	88	82	76	94	87	81	76	84	79	74		81	77	73		79	75	72	70
4	90	80	73	67	88	78	72	67	76	70	66		74	69	65		72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58		68	62	58		66	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		61	55	51	50
7	72	61	53	48	71	60	53	47	58	52	47		57	51	47		56	51	46	45
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36		45	40	35		45	39	35	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77826
5°	77802
10°	77549
15°	77059
20°	76107
25°	74447
30°	72305
35°	68741
40°	62946
45°	54233
50°	43298
55°	31598
60°	21360
65°	13400
70°	7573
75°	3126
80°	0
85°	0



TEST NUMBER: P303607

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSBZ 2000Lm4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	5.0
10°-20°	321.3	14.2
20°-30°	475.9	21.1
30°-40°	536.2	23.8
40°-50°	450.4	20.0
50°-60°	253.6	11.2
60°-70°	90.9	4.0
70°-80°	16.3	0.7
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	909.9	40.3
0°-40°	1446.1	64.1
0°-60°	2150.2	95.3
0°-90°	2257.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2257.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1193	
5°	1188	113
15°	1141	321
25°	1034	476
35°	863	536
45°	588	450
55°	278	254
65°	87	91
75°	12	16
85°	0	0
90°	0	



TEST NUMBER: P303607

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSBZ 2000Lm4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1192.9
2.5°	1190.5
5°	1188.0
7.5°	1180.5
10°	1170.6
12.5°	1155.7
15°	1140.9
17.5°	1118.5
20°	1096.2
22.5°	1066.5
25°	1034.2
27.5°	999.5
30°	959.8
32.5°	915.2
35°	863.1
37.5°	803.6
40°	739.1
42.5°	667.2
45°	587.8
47.5°	505.9
50°	426.6
52.5°	349.7
55°	277.8
57.5°	218.3
60°	163.7
62.5°	121.5
65°	86.8
67.5°	59.5
70°	39.7
72.5°	24.8
75°	12.4
77.5°	5.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)