

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345287

Luminaire Tested: **PR4FS12D010 PR4M12WD8FSMW 1000Lm3500K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P345287  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-4)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR4FS12D010 PR4M12WD8FSMW 1000Lm3500K  
Description: PR4 WIDE LENS WITH, MATTE WHITE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1016.0 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 1.61 / 1.61 / 1.58  
Luminous Opening: Circular (Dia: 0.4' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P345287

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMW 1000Lm3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P345287

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMW 1000Lm3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	73
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62
4	84	73	64	58	82	71	63	57	69	62	57	67	61	56	64	59	55	53
5	77	65	56	50	75	64	56	50	62	55	49	60	54	49	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	44	38	65	52	44	38	51	43	38	49	43	38	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	32
9	57	44	36	31	56	44	36	31	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	25585
5°	26482
10°	28635
15°	30644
20°	32635
25°	34310
30°	35037
35°	34949
40°	34438
45°	33300
50°	31312
55°	28273
60°	24404
65°	20014
70°	15958
75°	13011
80°	11737
85°	9835



TEST NUMBER: P345287

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMW 1000Lm3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.5	2.9
10°-20°	96.2	9.5
20°-30°	163.3	16.1
30°-40°	204.4	20.1
40°-50°	206.8	20.4
50°-60°	165.3	16.3
60°-70°	97.0	9.5
70°-80°	42.2	4.2
80°-90°	11.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.0	28.4
0°-40°	493.4	48.6
0°-60°	865.5	85.2
0°-90°	1016.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1016.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	292	
5°	302	29
15°	338	96
25°	356	163
35°	327	204
45°	269	207
55°	185	165
65°	97	97
75°	38	42
85°	10	11
90°	0	



TEST NUMBER: P345287

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMW 1000Lm3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	292.5
2.5°	294.9
5°	301.6
7.5°	312.0
10°	322.4
12.5°	331.6
15°	338.4
17.5°	345.1
20°	350.6
22.5°	354.3
25°	355.5
27.5°	353.0
30°	346.9
32.5°	337.7
35°	327.3
37.5°	315.7
40°	301.6
42.5°	287.0
45°	269.2
47.5°	250.2
50°	230.1
52.5°	208.0
55°	185.4
57.5°	162.1
60°	139.5
62.5°	116.9
65°	96.7
67.5°	78.3
70°	62.4
72.5°	48.9
75°	38.5
77.5°	30.0
80°	23.3
82.5°	16.5
85°	9.8
87.5°	3.7
90°	0.0

(END OF REPORT)