

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345364

Luminaire Tested: **PR4FS12D010 PR4M12WD8FSBZ 1500Lm3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P345364  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-6)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR4FS12D010 PR4M12WD8FSBZ 1500Lm3000K  
Description: PR4 WIDE LENS WITH, BRONZE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 995.0 lumens  
Efficiency: N/A  
Efficacy: 71.6 lumens/watt  
Spacing Criteria (0/90/45): 1.62 / 1.62 / 1.57  
Luminous Opening: Circular (Dia: 0.4' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P345364

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1500Lm3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P345364

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1500Lm3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76
3	94	85	77	72	91	83	76	71	80	74	70	77	73	69	75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	63	59	57
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	38
8	63	51	42	37	62	50	42	37	49	41	36	47	41	36	46	40	36	34
9	59	46	38	33	58	46	38	33	45	38	33	44	37	33	43	37	32	31
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26897
5°	27913
10°	30420
15°	32835
20°	35213
25°	37080
30°	37754
35°	37448
40°	36641
45°	34908
50°	31924
55°	27480
60°	21745
65°	15109
70°	8567
75°	3515
80°	756
85°	1505



TEST NUMBER: P345364

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1500Lm3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	31.2	3.1
10°-20°	103.1	10.4
20°-30°	176.3	17.7
30°-40°	219.0	22.0
40°-50°	216.2	21.7
50°-60°	160.4	16.1
60°-70°	74.1	7.4
70°-80°	13.5	1.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	310.6	31.2
0°-40°	529.6	53.2
0°-60°	906.2	91.1
0°-90°	995.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	995.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	308	
5°	318	31
15°	363	103
25°	384	176
35°	351	219
45°	282	216
55°	180	160
65°	73	74
75°	10	14
85°	2	1
90°	0	



TEST NUMBER: P345364

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1500Lm3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	307.5
2.5°	309.8
5°	317.9
7.5°	330.6
10°	342.5
12.5°	353.7
15°	362.6
17.5°	370.8
20°	378.3
22.5°	382.7
25°	384.2
27.5°	381.2
30°	373.8
32.5°	363.4
35°	350.7
37.5°	337.3
40°	320.9
42.5°	302.3
45°	282.2
47.5°	259.1
50°	234.6
52.5°	207.7
55°	180.2
57.5°	151.9
60°	124.3
62.5°	97.5
65°	73.0
67.5°	51.4
70°	33.5
72.5°	20.1
75°	10.4
77.5°	3.7
80°	1.5
82.5°	1.5
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)