

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345328

Luminaire Tested: **PR4FS12D010 PR4M12WD8FSMMS 1500Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P345328
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-5)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR4FS12D010 PR4M12WD8FSMMS 1500Lm3000K
Description: PR4 WIDE LENS WITH, MATTE METALLIC SILVER FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1152.8 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.65 / 1.65 / 1.6
Luminous Opening: Circular (Dia: 0.4' x H: 0')
CIE Type: Direct


Input Watts (W): 13.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P345328

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMMS 1500lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P345328

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMMS 1500Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	107	104	100	97	100	97	94	96	93	91	92	90	89	87
2	101	94	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74
3	92	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	60	56	54
5	78	66	57	51	76	65	57	51	63	56	50	61	54	50	59	53	49	47
6	72	59	51	44	70	58	50	44	57	49	44	55	48	43	53	48	43	41
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38	36
8	62	49	41	35	61	48	40	35	47	40	35	46	39	34	44	39	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	33	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28839
5°	29862
10°	32588
15°	35108
20°	37615
25°	39937
30°	40895
35°	41089
40°	40615
45°	39213
50°	36659
55°	32680
60°	27343
65°	21256
70°	15217
75°	10578
80°	7505
85°	5219



TEST NUMBER: P345328

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMMS 1500Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.4	2.9
10°-20°	110.3	9.6
20°-30°	189.9	16.5
30°-40°	240.0	20.8
40°-50°	243.5	21.1
50°-60°	190.8	16.6
60°-70°	103.2	8.9
70°-80°	35.3	3.1
80°-90°	6.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	333.5	28.9
0°-40°	573.5	49.7
0°-60°	1007.7	87.4
0°-90°	1152.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1152.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	330	
5°	340	33
15°	388	110
25°	414	190
35°	385	240
45°	317	243
55°	214	191
65°	103	103
75°	31	35
85°	5	7
90°	0	



TEST NUMBER: P345328

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMMS 1500Lm3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	329.7
2.5°	331.9
5°	340.1
7.5°	353.5
10°	366.9
12.5°	378.8
15°	387.7
17.5°	396.7
20°	404.1
22.5°	410.8
25°	413.8
27.5°	411.5
30°	404.9
32.5°	395.2
35°	384.8
37.5°	371.4
40°	355.7
42.5°	337.9
45°	317.0
47.5°	294.7
50°	269.4
52.5°	242.6
55°	214.3
57.5°	185.3
60°	156.3
62.5°	128.7
65°	102.7
67.5°	78.9
70°	59.5
72.5°	43.9
75°	31.3
77.5°	21.6
80°	14.9
82.5°	9.7
85°	5.2
87.5°	2.2
90°	0.0

(END OF REPORT)