

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303451

Luminaire Tested: **PR6FS24D010 PR6M24WD8FSBZ 2000Lm4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-6)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS24D010 PR6M24WD8FSBZ 2000Lm4000K
Description: PR6 WIDE LENS WITH, BRONZE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2235.3 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.26
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303451

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSBZ 2000Lm4000K

Luminous Intensity Polar Plot





TEST NUMBER: P303451

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSBZ 2000Lm4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50
7	73	61	54	48	71	61	53	48	59	53	48	58	52	48	56	51	47	46
8	68	56	49	44	67	56	49	44	55	48	43	53	48	43	52	47	43	41
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72293
5°	73873
10°	76038
15°	77694
20°	78655
25°	78874
30°	77315
35°	71871
40°	62282
45°	49407
50°	36732
55°	27071
60°	19729
65°	13400
70°	8507
75°	3756
80°	939
85°	0



TEST NUMBER: P303451

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSBZ 2000Lm4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.3	4.8
10°-20°	325.0	14.5
20°-30°	503.0	22.5
30°-40°	558.0	25.0
40°-50°	413.9	18.5
50°-60°	217.6	9.7
60°-70°	90.1	4.0
70°-80°	19.2	0.9
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.3	41.9
0°-40°	1494.3	66.8
0°-60°	2125.7	95.1
0°-90°	2235.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2235.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1108	
5°	1128	108
15°	1150	325
25°	1096	503
35°	902	558
45°	536	414
55°	238	218
65°	87	90
75°	15	19
85°	0	0
90°	0	



TEST NUMBER: P303451

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSBZ 2000Lm4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1108.1
2.5°	1115.6
5°	1128.0
7.5°	1140.4
10°	1147.8
12.5°	1152.7
15°	1150.3
17.5°	1145.3
20°	1132.9
22.5°	1118.0
25°	1095.7
27.5°	1066.0
30°	1026.3
32.5°	974.3
35°	902.4
37.5°	820.6
40°	731.3
42.5°	632.2
45°	535.5
47.5°	443.7
50°	361.9
52.5°	292.5
55°	238.0
57.5°	190.9
60°	151.2
62.5°	116.5
65°	86.8
67.5°	64.5
70°	44.6
72.5°	29.7
75°	14.9
77.5°	5.0
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)