

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345366

Luminaire Tested: **PR4FS12D010 PR4M12WD8FSBZ 1500Lm4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P345366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-6)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR4FS12D010 PR4M12WD8FSBZ 1500Lm4000K
Description: PR4 WIDE LENS WITH, BRONZE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1056.2 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.62 / 1.62 / 1.57
Luminous Opening: Circular (Dia: 0.4' x H: 0')
CIE Type: Direct


Input Watts (W): 13.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P345366

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1500Lm4000K

Luminous Intensity Polar Plot





TEST NUMBER: P345366

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1500Lm4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76
3	94	85	77	72	91	83	76	71	80	74	70	77	73	69	75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	63	59	57
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	38
8	63	51	42	37	62	50	42	37	49	41	36	47	41	36	46	40	36	34
9	59	46	38	33	58	46	38	33	45	38	33	44	37	33	43	37	32	31
10	55	43	35	30	54	42	35	30	41	34	30	40	34	30	39	34	29	28

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28550
5°	29634
10°	32286
15°	34855
20°	37373
25°	39358
30°	40067
35°	39744
40°	38891
45°	37048
50°	33883
55°	29173
60°	23092
65°	16040
70°	9104
75°	3751
80°	806
85°	1606



TEST NUMBER: P345366

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1500Lm4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.1	3.1
10°-20°	109.4	10.4
20°-30°	187.1	17.7
30°-40°	232.5	22.0
40°-50°	229.5	21.7
50°-60°	170.2	16.1
60°-70°	78.6	7.4
70°-80°	14.4	1.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	329.7	31.2
0°-40°	562.1	53.2
0°-60°	961.8	91.1
0°-90°	1056.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1056.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	326	
5°	338	33
15°	385	109
25°	408	187
35°	372	232
45°	300	229
55°	191	170
65°	78	79
75°	11	14
85°	2	1
90°	0	



TEST NUMBER: P345366

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSBZ 1500Lm4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	326.4
2.5°	328.8
5°	337.5
7.5°	350.9
10°	363.5
12.5°	375.4
15°	384.9
17.5°	393.6
20°	401.5
22.5°	406.2
25°	407.8
27.5°	404.6
30°	396.7
32.5°	385.7
35°	372.2
37.5°	358.0
40°	340.6
42.5°	320.9
45°	299.5
47.5°	275.0
50°	249.0
52.5°	220.5
55°	191.3
57.5°	161.2
60°	132.0
62.5°	103.5
65°	77.5
67.5°	54.5
70°	35.6
72.5°	21.3
75°	11.1
77.5°	4.0
80°	1.6
82.5°	1.6
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)