

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303335

Luminaire Tested: **PR6FS24D010 PR6M24MD8FSMMS 3000Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS24D010 PR6M24MD8FSMMS 3000Lm3000K
Description: PR6 MEDIUM LENS WITH, MATTE METALLIC SILVER FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2615.5 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 28.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303335

CATALOG NUMBER: PR6FS24D010 PR6M24MD8FSMMS 3000Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P303335

CATALOG NUMBER: PR6FS24D010 PR6M24MD8FSMMS 3000Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	96	87	81	75	94	86	80	75	83	78	74	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	45	41	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87703
5°	87684
10°	87261
15°	86596
20°	85632
25°	84115
30°	82113
35°	77980
40°	72101
45°	62638
50°	50515
55°	38150
60°	26827
65°	17954
70°	11350
75°	6806
80°	4058
85°	2021



TEST NUMBER: P303335

CATALOG NUMBER: PR6FS24D010 PR6M24MD8FSMMS 3000Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.0	4.9
10°-20°	361.6	13.8
20°-30°	537.8	20.6
30°-40°	610.0	23.3
40°-50°	519.2	19.8
50°-60°	303.8	11.6
60°-70°	120.6	4.6
70°-80°	32.0	1.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1026.4	39.2
0°-40°	1636.4	62.6
0°-60°	2459.3	94.0
0°-90°	2615.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2615.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1344	
5°	1339	127
15°	1282	362
25°	1168	538
35°	979	610
45°	679	519
55°	335	304
65°	116	121
75°	27	32
85°	3	4
90°	0	



TEST NUMBER: P303335

CATALOG NUMBER: PR6FS24D010 PR6M24MD8FSMMS 3000Lm3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1344.3
2.5°	1341.6
5°	1338.9
7.5°	1328.1
10°	1317.2
12.5°	1301.0
15°	1282.1
17.5°	1260.4
20°	1233.4
22.5°	1203.6
25°	1168.5
27.5°	1130.6
30°	1090.0
32.5°	1038.7
35°	979.1
37.5°	916.9
40°	846.6
42.5°	765.5
45°	678.9
47.5°	584.2
50°	497.7
52.5°	413.8
55°	335.4
57.5°	265.1
60°	205.6
62.5°	156.9
65°	116.3
67.5°	83.8
70°	59.5
72.5°	43.3
75°	27.0
77.5°	16.2
80°	10.8
82.5°	5.4
85°	2.7
87.5°	0.0
90°	0.0

(END OF REPORT)