

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345298

Luminaire Tested: **PR4FS12D010 PR4M12WD8FSMW 2000Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P345298
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-4)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR4FS12D010 PR4M12WD8FSMW 2000Lm3000K
Description: PR4 WIDE LENS WITH, MATTE WHITE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2002.2 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.61 / 1.61 / 1.58
Luminous Opening: Circular (Dia: 0.4' x H: 0')
CIE Type: Direct


Input Watts (W): 20.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P345298

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMW 2000Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P345298

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMW 2000Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93		95	93	90		91	90	88	86
2	100	93	86	81	98	91	85	80	87	82	78		84	80	76		81	78	75	73
3	92	82	74	68	89	80	73	67	77	71	66		75	69	65		72	68	64	62
4	84	73	64	58	82	71	63	57	69	62	57		67	61	56		64	59	55	53
5	77	65	56	50	75	64	56	50	62	55	49		60	54	49		58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43		54	48	43		53	47	42	40
7	66	53	44	38	65	52	44	38	51	43	38		49	43	38		48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		44	38	33	32
9	57	44	36	31	56	44	36	31	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27		38	32	27		37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50409
5°	52190
10°	56435
15°	60373
20°	64311
25°	67607
30°	69044
35°	68873
40°	67871
45°	65623
50°	61684
55°	55708
60°	48091
65°	39428
70°	31456
75°	25685
80°	23070
85°	19369



TEST NUMBER: P345298

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMW 2000Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	2.9
10°-20°	189.5	9.5
20°-30°	321.8	16.1
30°-40°	402.8	20.1
40°-50°	407.6	20.4
50°-60°	325.7	16.3
60°-70°	191.1	9.5
70°-80°	83.3	4.2
80°-90°	22.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	569.4	28.4
0°-40°	972.2	48.6
0°-60°	1705.5	85.2
0°-90°	2002.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2002.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	576	
5°	594	58
15°	667	190
25°	700	322
35°	645	403
45°	530	408
55°	365	326
65°	190	191
75°	76	83
85°	19	22
90°	0	



TEST NUMBER: P345298

CATALOG NUMBER: PR4FS12D010 PR4M12WD8FSMW 2000Lm3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	576.3
2.5°	581.1
5°	594.4
7.5°	614.9
10°	635.4
12.5°	653.5
15°	666.7
17.5°	680.0
20°	690.9
22.5°	698.1
25°	700.5
27.5°	695.7
30°	683.6
32.5°	665.5
35°	645.0
37.5°	622.1
40°	594.4
42.5°	565.5
45°	530.5
47.5°	493.1
50°	453.3
52.5°	409.9
55°	365.3
57.5°	319.5
60°	274.9
62.5°	230.3
65°	190.5
67.5°	154.3
70°	123.0
72.5°	96.5
75°	76.0
77.5°	59.1
80°	45.8
82.5°	32.6
85°	19.3
87.5°	7.2
90°	0.0

(END OF REPORT)