

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303456

Luminaire Tested: **PR6FS24D010 PR6M24WD8FSBZ 3000Lm3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303456
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-6)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS24D010 PR6M24WD8FSBZ 3000Lm3500K
Description: PR6 WIDE LENS WITH, BRONZE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3020.7 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.26
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 26.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303456

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSBZ 3000Lm3500K

Luminous Intensity Polar Plot





TEST NUMBER: P303456

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSBZ 3000Lm3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50
7	73	61	54	48	71	61	53	48	59	53	48	58	52	48	56	51	47	46
8	68	56	49	44	67	56	49	44	55	48	43	53	48	43	52	47	43	41
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97698
5°	99826
10°	102756
15°	104987
20°	106294
25°	106588
30°	104480
35°	97118
40°	84169
45°	66762
50°	49642
55°	36580
60°	26670
65°	18108
70°	11502
75°	5067
80°	1277
85°	0



TEST NUMBER: P303456

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSBZ 3000Lm3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.4	4.8
10°-20°	439.2	14.5
20°-30°	679.8	22.5
30°-40°	754.0	25.0
40°-50°	559.3	18.5
50°-60°	294.0	9.7
60°-70°	121.7	4.0
70°-80°	25.9	0.9
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1265.3	41.9
0°-40°	2019.3	66.8
0°-60°	2872.6	95.1
0°-90°	3020.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3020.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1498	
5°	1524	146
15°	1554	439
25°	1481	680
35°	1219	754
45°	724	559
55°	322	294
65°	117	122
75°	20	26
85°	0	0
90°	0	



TEST NUMBER: P303456

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSBZ 3000Lm3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1497.5
2.5°	1507.5
5°	1524.3
7.5°	1541.0
10°	1551.1
12.5°	1557.8
15°	1554.4
17.5°	1547.7
20°	1531.0
22.5°	1510.9
25°	1480.7
27.5°	1440.5
30°	1386.9
32.5°	1316.6
35°	1219.4
37.5°	1108.9
40°	988.3
42.5°	854.3
45°	723.6
47.5°	599.7
50°	489.1
52.5°	395.3
55°	321.6
57.5°	258.0
60°	204.4
62.5°	157.5
65°	117.3
67.5°	87.1
70°	60.3
72.5°	40.2
75°	20.1
77.5°	6.7
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)