

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345301

Luminaire Tested: **PR4FS12D010 PR4M12WD9FSMW 2000Lm3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P345301  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-4)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR4FS12D010 PR4M12WD9FSMW 2000Lm3000K  
Description: PR4 WIDE LENS WITH, MATTE WHITE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1707.2 lumens  
Efficiency: N/A  
Efficacy: 82.5 lumens/watt  
Spacing Criteria (0/90/45): 1.61 / 1.61 / 1.58  
Luminous Opening: Circular (Dia: 0.4' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P345301

CATALOG NUMBER: PR4FS12D010 PR4M12WD9FSMW 2000Lm3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P345301

CATALOG NUMBER: PR4FS12D010 PR4M12WD9FSMW 2000Lm3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93		95	93	90		91	90	88	86
2	100	93	86	81	98	91	85	80	87	82	78		84	80	76		81	78	75	73
3	92	82	74	68	89	80	73	67	77	71	66		75	69	65		72	68	64	62
4	84	73	64	58	82	71	63	57	69	62	57		67	61	56		64	59	55	53
5	77	65	56	50	75	64	56	50	62	55	49		60	54	49		58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43		54	48	43		53	47	42	40
7	66	53	44	38	65	52	44	38	51	43	38		49	43	38		48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		44	38	33	32
9	57	44	36	31	56	44	36	31	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27		38	32	27		37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	42982
5°	44499
10°	48122
15°	51481
20°	54835
25°	57647
30°	58873
35°	58729
40°	57868
45°	55950
50°	52594
55°	47503
60°	41006
65°	33612
70°	26827
75°	21900
80°	19695
85°	16459



TEST NUMBER: P345301

CATALOG NUMBER: PR4FS12D010 PR4M12WD9FSMW 2000Lm3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.6	2.9
10°-20°	161.6	9.5
20°-30°	274.4	16.1
30°-40°	343.5	20.1
40°-50°	347.5	20.4
50°-60°	277.7	16.3
60°-70°	163.0	9.5
70°-80°	71.0	4.2
80°-90°	19.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	485.5	28.4
0°-40°	829.0	48.6
0°-60°	1454.2	85.2
0°-90°	1707.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1707.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	491	
5°	507	50
15°	568	162
25°	597	274
35°	550	343
45°	452	348
55°	312	278
65°	162	163
75°	65	71
85°	16	19
90°	0	



TEST NUMBER: P345301

CATALOG NUMBER: PR4FS12D010 PR4M12WD9FSMW 2000Lm3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	491.4
2.5°	495.5
5°	506.8
7.5°	524.3
10°	541.8
12.5°	557.2
15°	568.5
17.5°	579.8
20°	589.1
22.5°	595.2
25°	597.3
27.5°	593.2
30°	582.9
32.5°	567.5
35°	550.0
37.5°	530.5
40°	506.8
42.5°	482.2
45°	452.3
47.5°	420.5
50°	386.5
52.5°	349.5
55°	311.5
57.5°	272.4
60°	234.4
62.5°	196.4
65°	162.4
67.5°	131.6
70°	104.9
72.5°	82.2
75°	64.8
77.5°	50.4
80°	39.1
82.5°	27.8
85°	16.4
87.5°	6.2
90°	0.0

(END OF REPORT)