

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210219

Luminaire Tested: **PR820D010 - PR8M12WDMMS - 3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR820D010 - PR8M12WDMMS - 3000K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE METALLIC SILVER FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2093.4 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210219

CATALOG NUMBER: PR820D010 - PR8M12WDMMS - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P210219

CATALOG NUMBER: PR820D010 - PR8M12WDMMS - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25400
5°	25825
10°	26136
15°	26622
20°	27181
25°	27430
30°	27389
35°	27322
40°	26370
45°	24151
50°	20177
55°	16774
60°	14098
65°	11645
70°	10017
75°	7863
80°	5434
85°	5732



TEST NUMBER: P210219

CATALOG NUMBER: PR820D010 - PR8M12WDMMS - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.5	3.8
10°-20°	236.0	11.3
20°-30°	370.6	17.7
30°-40°	451.7	21.6
40°-50°	422.2	20.2
50°-60°	281.6	13.5
60°-70°	162.0	7.7
70°-80°	74.7	3.6
80°-90°	15.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	686.0	32.8
0°-40°	1137.7	54.3
0°-60°	1841.5	88.0
0°-90°	2093.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2093.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	824	
5°	834	79
15°	834	236
25°	806	371
35°	726	452
45°	554	422
55°	312	282
65°	160	162
75°	66	75
85°	16	15
90°	0	



TEST NUMBER: P210219

CATALOG NUMBER: PR820D010 - PR8M12WDMMS - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	823.7
2.5°	824.9
5°	834.3
7.5°	833.5
10°	834.7
12.5°	833.0
15°	833.9
17.5°	832.2
20°	828.3
22.5°	814.7
25°	806.2
27.5°	789.2
30°	769.2
32.5°	749.2
35°	725.8
37.5°	697.7
40°	655.1
42.5°	608.7
45°	553.8
47.5°	492.9
50°	420.6
52.5°	359.3
55°	312.0
57.5°	266.9
60°	228.6
62.5°	195.4
65°	159.6
67.5°	131.1
70°	111.1
72.5°	94.5
75°	66.0
77.5°	52.4
80°	30.6
82.5°	19.6
85°	16.2
87.5°	4.7
90°	0.0

(END OF REPORT)