

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P345354

Luminaire Tested: **PR4FS24D010 PR4M24WD8FSMMS 4000Lm4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P345354
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1908-453-5)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR4FS24D010 PR4M24WD8FSMMS 4000Lm4000K
Description: PR4 WIDE LENS WITH, MATTE METALLIC SILVER FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3587.5 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 1.65 / 1.65 / 1.6
Luminous Opening: Circular (Dia: 0.4' x H: 0')
CIE Type: Direct


Input Watts (W): 45
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P345354

CATALOG NUMBER: PR4FS24D010 PR4M24WD8FSMMS 4000Lm4000K

Luminous Intensity Polar Plot





TEST NUMBER: P345354

CATALOG NUMBER: PR4FS24D010 PR4M24WD8FSMMS 4000Lm4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	107	104	100	97	100	97	94	96	93	91	92	90	89	87
2	101	94	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74
3	92	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	65	60	56	54
5	78	66	57	51	76	65	57	51	63	56	50	61	54	50	59	53	49	47
6	72	59	51	44	70	58	50	44	57	49	44	55	48	43	53	48	43	41
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	49	43	38	36
8	62	49	41	35	61	48	40	35	47	40	35	46	39	34	44	39	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	33	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89735
5°	92931
10°	101404
15°	109264
20°	117052
25°	124269
30°	127241
35°	127848
40°	126401
45°	122043
50°	114088
55°	101716
60°	85073
65°	66148
70°	47389
75°	32883
80°	23322
85°	16258



TEST NUMBER: P345354

CATALOG NUMBER: PR4FS24D010 PR4M24WD8FSMMS 4000Lm4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.9	2.9
10°-20°	343.2	9.6
20°-30°	590.8	16.5
30°-40°	746.7	20.8
40°-50°	757.6	21.1
50°-60°	593.8	16.6
60°-70°	321.1	8.9
70°-80°	109.7	3.1
80°-90°	20.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1037.9	28.9
0°-40°	1784.5	49.7
0°-60°	3136.0	87.4
0°-90°	3587.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3587.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1026	
5°	1058	104
15°	1207	343
25°	1288	591
35°	1197	747
45°	987	758
55°	667	594
65°	320	321
75°	97	110
85°	16	21
90°	0	



TEST NUMBER: P345354

CATALOG NUMBER: PR4FS24D010 PR4M24WD8FSMMS 4000Lm4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1025.9
2.5°	1032.9
5°	1058.4
7.5°	1100.1
10°	1141.7
12.5°	1178.8
15°	1206.6
17.5°	1234.4
20°	1257.5
22.5°	1278.4
25°	1287.6
27.5°	1280.7
30°	1259.8
32.5°	1229.7
35°	1197.3
37.5°	1155.6
40°	1107.0
42.5°	1051.4
45°	986.6
47.5°	917.1
50°	838.4
52.5°	755.0
55°	667.0
57.5°	576.7
60°	486.3
62.5°	400.7
65°	319.6
67.5°	245.5
70°	185.3
72.5°	136.6
75°	97.3
77.5°	67.2
80°	46.3
82.5°	30.1
85°	16.2
87.5°	6.9
90°	0.0

(END OF REPORT)