

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303317

Luminaire Tested: **PR6FS12D010 PR6M12MD8FSMMS 1000Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303317
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12MD8FSMMS 1000Lm3000K
Description: PR6 MEDIUM LENS WITH, MATTE METALLIC SILVER FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1121.6 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 10.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303317

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSMMS 1000Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P303317

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSMMS 1000Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84		89	85	82		86	83	81	79
3	96	87	81	75	94	86	80	75	83	78	74		80	76	72		78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65		73	68	64		71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	65	58	52	75	64	57	52	63	56	51		61	55	51		60	55	51	49
7	72	60	52	47	70	59	52	46	58	51	46		56	50	46		55	50	46	44
8	67	55	47	42	66	54	47	42	53	47	42		52	46	42		51	45	41	40
9	63	51	43	38	62	50	43	38	49	43	38		48	42	38		47	42	38	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37611
5°	37598
10°	37423
15°	37135
20°	36720
25°	36072
30°	35211
35°	33443
40°	30915
45°	26858
50°	21659
55°	16356
60°	11508
65°	7703
70°	4864
75°	2924
80°	1728
85°	898



TEST NUMBER: P303317

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSMMS 1000Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	4.9
10°-20°	155.0	13.8
20°-30°	230.6	20.6
30°-40°	261.6	23.3
40°-50°	222.6	19.8
50°-60°	130.3	11.6
60°-70°	51.7	4.6
70°-80°	13.7	1.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	440.1	39.2
0°-40°	701.7	62.6
0°-60°	1054.6	94.0
0°-90°	1121.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1121.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	576	
5°	574	54
15°	550	155
25°	501	231
35°	420	262
45°	291	223
55°	144	130
65°	50	52
75°	12	14
85°	1	2
90°	0	



TEST NUMBER: P303317

CATALOG NUMBER: PR6FS12D010 PR6M12MD8FSMMS 1000Lm3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	576.5
2.5°	575.3
5°	574.1
7.5°	569.5
10°	564.9
12.5°	557.9
15°	549.8
17.5°	540.5
20°	528.9
22.5°	516.1
25°	501.1
27.5°	484.8
30°	467.4
32.5°	445.4
35°	419.9
37.5°	393.2
40°	363.0
42.5°	328.2
45°	291.1
47.5°	250.5
50°	213.4
52.5°	177.5
55°	143.8
57.5°	113.7
60°	88.2
62.5°	67.3
65°	49.9
67.5°	36.0
70°	25.5
72.5°	18.6
75°	11.6
77.5°	7.0
80°	4.6
82.5°	2.3
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)