

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210316

Luminaire Tested: **PR8R10D010 - PR8M12MDMW - 4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8R10D010 - PR8M12MDMW - 4000K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE WHITE FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1244.8 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210316

CATALOG NUMBER: PR8R10D010 - PR8M12MDMW - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P210316

CATALOG NUMBER: PR8R10D010 - PR8M12MDMW - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63		72	67	62		70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21456
5°	21383
10°	20826
15°	19969
20°	18839
25°	17842
30°	16482
35°	15050
40°	14049
45°	12834
50°	12137
55°	10930
60°	8542
65°	5947
70°	3778
75°	2133
80°	604
85°	0



TEST NUMBER: P210316

CATALOG NUMBER: PR8R10D010 - PR8M12MDMW - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	5.2
10°-20°	175.2	14.1
20°-30°	240.0	19.3
30°-40°	251.5	20.2
40°-50°	229.3	18.4
50°-60°	178.9	14.4
60°-70°	83.3	6.7
70°-80°	20.8	1.7
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.3	38.6
0°-40°	731.9	58.8
0°-60°	1140.1	91.6
0°-90°	1244.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1244.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	696	
5°	691	65
15°	626	175
25°	524	240
35°	400	252
45°	294	229
55°	203	179
65°	82	83
75°	18	21
85°	0	1
90°	0	



TEST NUMBER: P210316

CATALOG NUMBER: PR8R10D010 - PR8M12MDMW - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	695.8
2.5°	692.5
5°	690.8
7.5°	682.4
10°	665.1
12.5°	645.0
15°	625.5
17.5°	600.9
20°	574.1
22.5°	548.9
25°	524.4
27.5°	494.8
30°	462.9
32.5°	430.6
35°	399.8
37.5°	374.2
40°	349.0
42.5°	322.2
45°	294.3
47.5°	272.0
50°	253.0
52.5°	231.8
55°	203.3
57.5°	171.4
60°	138.5
62.5°	107.2
65°	81.5
67.5°	59.2
70°	41.9
72.5°	28.5
75°	17.9
77.5°	10.1
80°	3.4
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)