

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303380

Luminaire Tested: **PR6FS12D010 PR6M12WD9FSMW 1000Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-4)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12WD9FSMW 1000Lm3000K
Description: PR6 WIDE LENS WITH, MATTE WHITE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1027.9 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.33 / 1.33 / 1.28
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 10.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303380

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSMW 1000Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P303380

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSMW 1000Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	98	96		97	95	93		94	92	91	89
2	103	96	91	86	101	94	89	85	91	87	83		88	84	81		85	82	80	78
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	88	78	71	65	86	77	70	65	75	69	64		72	67	63		70	66	62	60
5	82	71	63	57	80	70	63	57	68	61	57		66	60	56		64	59	55	54
6	76	65	57	51	75	64	56	51	62	55	51		61	55	50		59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45		56	50	45		54	49	45	43
8	67	54	47	42	65	54	47	41	53	46	41		51	45	41		50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	35
10	59	47	39	35	58	46	39	34	45	39	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30676
5°	31389
10°	32415
15°	33183
20°	33624
25°	33775
30°	33388
35°	31300
40°	27500
45°	22476
50°	17508
55°	13683
60°	10856
65°	8660
70°	6886
75°	5571
80°	4508
85°	2994



TEST NUMBER: P303380

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSMW 1000Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.1	4.5
10°-20°	138.7	13.5
20°-30°	215.8	21.0
30°-40°	243.2	23.7
40°-50°	188.6	18.4
50°-60°	109.6	10.7
60°-70°	56.8	5.5
70°-80°	24.0	2.3
80°-90°	5.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	400.5	39.0
0°-40°	643.7	62.6
0°-60°	941.9	91.6
0°-90°	1027.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1027.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	470	
5°	479	46
15°	491	139
25°	469	216
35°	393	243
45°	244	189
55°	120	110
65°	56	57
75°	22	24
85°	4	5
90°	0	



TEST NUMBER: P303380

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSMW 1000Lm3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	470.2
2.5°	473.3
5°	479.3
7.5°	485.3
10°	489.3
12.5°	491.3
15°	491.3
17.5°	488.3
20°	484.3
22.5°	478.3
25°	469.2
27.5°	458.2
30°	443.2
32.5°	422.1
35°	393.0
37.5°	360.0
40°	322.9
42.5°	284.8
45°	243.6
47.5°	206.5
50°	172.5
52.5°	143.4
55°	120.3
57.5°	100.3
60°	83.2
62.5°	68.2
65°	56.1
67.5°	46.1
70°	36.1
72.5°	29.1
75°	22.1
77.5°	16.0
80°	12.0
82.5°	8.0
85°	4.0
87.5°	1.0
90°	0.0

(END OF REPORT)