

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210376

Luminaire Tested: **PR8R10D010 - PR8M12WDMB - 4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8R10D010 - PR8M12WDMB - 4000K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE BLACK FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1124.7 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210376

CATALOG NUMBER: PR8R10D010 - PR8M12WDMB - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P210376

CATALOG NUMBER: PR8R10D010 - PR8M12WDMB - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13645
5°	13877
10°	14043
15°	14302
20°	14606
25°	14739
30°	14716
35°	14677
40°	14169
45°	12974
50°	10842
55°	9010
60°	7573
65°	6260
70°	5383
75°	4218
80°	2930
85°	3078



TEST NUMBER: P210376

CATALOG NUMBER: PR8R10D010 - PR8M12WDMB - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	3.8
10°-20°	126.8	11.3
20°-30°	199.1	17.7
30°-40°	242.7	21.6
40°-50°	226.8	20.2
50°-60°	151.3	13.5
60°-70°	87.0	7.7
70°-80°	40.1	3.6
80°-90°	8.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	368.6	32.8
0°-40°	611.3	54.3
0°-60°	989.4	88.0
0°-90°	1124.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	442	
5°	448	43
15°	448	127
25°	433	199
35°	390	243
45°	298	227
55°	168	151
65°	86	87
75°	35	40
85°	9	8
90°	0	



TEST NUMBER: P210376

CATALOG NUMBER: PR8R10D010 - PR8M12WDMB - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	442.5
2.5°	443.2
5°	448.3
7.5°	447.8
10°	448.5
12.5°	447.6
15°	448.0
17.5°	447.1
20°	445.1
22.5°	437.7
25°	433.2
27.5°	424.0
30°	413.3
32.5°	402.5
35°	389.9
37.5°	374.8
40°	352.0
42.5°	327.0
45°	297.5
47.5°	264.8
50°	226.0
52.5°	193.0
55°	167.6
57.5°	143.4
60°	122.8
62.5°	105.0
65°	85.8
67.5°	70.4
70°	59.7
72.5°	50.8
75°	35.4
77.5°	28.1
80°	16.5
82.5°	10.5
85°	8.7
87.5°	2.5
90°	0.0

(END OF REPORT)