

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303322

Luminaire Tested: **PR6FS12D010 PR6M12MD9FSMMS 1000Lm4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303322
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12MD9FSMMS 1000Lm4000K
Description: PR6 MEDIUM LENS WITH, MATTE METALLIC SILVER FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 948.0 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 10.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303322

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 1000Lm4000K

Luminous Intensity Polar Plot





TEST NUMBER: P303322

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 1000Lm4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	96	87	81	75	94	86	80	75	83	78	74	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	45	41	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31785
5°	31776
10°	31626
15°	31387
20°	31034
25°	30486
30°	29764
35°	28266
40°	26129
45°	22706
50°	18310
55°	13831
60°	9721
65°	6515
70°	4120
75°	2470
80°	1465
85°	749



TEST NUMBER: P303322

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 1000Lm4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	4.9
10°-20°	131.0	13.8
20°-30°	194.9	20.6
30°-40°	221.1	23.3
40°-50°	188.2	19.8
50°-60°	110.1	11.6
60°-70°	43.7	4.6
70°-80°	11.6	1.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.0	39.2
0°-40°	593.1	62.6
0°-60°	891.4	94.0
0°-90°	948.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	948.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	487	
5°	485	46
15°	465	131
25°	424	195
35°	355	221
45°	246	188
55°	122	110
65°	42	44
75°	10	12
85°	1	1
90°	0	



TEST NUMBER: P303322

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSMMS 1000Lm4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	487.2
2.5°	486.2
5°	485.2
7.5°	481.3
10°	477.4
12.5°	471.5
15°	464.7
17.5°	456.8
20°	447.0
22.5°	436.2
25°	423.5
27.5°	409.8
30°	395.1
32.5°	376.4
35°	354.9
37.5°	332.3
40°	306.8
42.5°	277.4
45°	246.1
47.5°	211.7
50°	180.4
52.5°	150.0
55°	121.6
57.5°	96.1
60°	74.5
62.5°	56.9
65°	42.2
67.5°	30.4
70°	21.6
72.5°	15.7
75°	9.8
77.5°	5.9
80°	3.9
82.5°	2.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)