

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303356

Luminaire Tested: **PR6FS12D010 PR6M12MD9FSBZ 1500Lm3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P303356  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-3)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR6FS12D010 PR6M12MD9FSBZ 1500Lm3000K  
Description: PR6 MEDIUM LENS WITH, BRONZE FINISH  
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1169.4 lumens  
Efficiency: N/A  
Efficacy: 84.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P303356

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSBZ 1500Lm3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P303356

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSBZ 1500Lm3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86	84	81	79
3	97	88	82	76	94	87	81	76	84	79	74		81	77	73		79	75	72	70
4	90	80	73	67	88	78	72	67	76	70	66		74	69	65		72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58		68	62	58		66	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		61	55	51	50
7	72	61	53	48	71	60	53	47	58	52	47		57	51	47		56	51	46	45
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36		45	40	35		45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	40319
5°	40302
10°	40172
15°	39917
20°	39428
25°	38562
30°	37456
35°	35609
40°	32610
45°	28094
50°	22431
55°	16368
60°	11065
65°	6947
70°	3929
75°	1613
80°	0
85°	0



TEST NUMBER: P303356

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSBZ 1500Lm3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.4	5.0
10°-20°	166.4	14.2
20°-30°	246.5	21.1
30°-40°	277.8	23.8
40°-50°	233.3	20.0
50°-60°	131.4	11.2
60°-70°	47.1	4.0
70°-80°	8.4	0.7
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	471.4	40.3
0°-40°	749.1	64.1
0°-60°	1113.9	95.3
0°-90°	1169.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1169.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	618	
5°	615	58
15°	591	166
25°	536	247
35°	447	278
45°	304	233
55°	144	131
65°	45	47
75°	6	8
85°	0	0
90°	0	



TEST NUMBER: P303356

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSBZ 1500Lm3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	618.0
2.5°	616.7
5°	615.4
7.5°	611.5
10°	606.4
12.5°	598.7
15°	591.0
17.5°	579.4
20°	567.9
22.5°	552.4
25°	535.7
27.5°	517.8
30°	497.2
32.5°	474.1
35°	447.1
37.5°	416.3
40°	382.9
42.5°	345.6
45°	304.5
47.5°	262.1
50°	221.0
52.5°	181.1
55°	143.9
57.5°	113.1
60°	84.8
62.5°	63.0
65°	45.0
67.5°	30.8
70°	20.6
72.5°	12.8
75°	6.4
77.5°	2.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)