

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210335

Luminaire Tested: **PR8R15D010 - PR8M12MDMB - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8R15D010 - PR8M12MDMB - 3500K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE BLACK FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1640.7 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 15
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210335

CATALOG NUMBER: PR8R15D010 - PR8M12MDMB - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210335

CATALOG NUMBER: PR8R15D010 - PR8M12MDMB - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63		72	67	62		70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28283
5°	28187
10°	27451
15°	26318
20°	24831
25°	23517
30°	21727
35°	19838
40°	18521
45°	16916
50°	15999
55°	14403
60°	11261
65°	7844
70°	4977
75°	2812
80°	781
85°	0



TEST NUMBER: P210335

CATALOG NUMBER: PR8R15D010 - PR8M12MDMB - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.9	5.2
10°-20°	231.0	14.1
20°-30°	316.3	19.3
30°-40°	331.6	20.2
40°-50°	302.2	18.4
50°-60°	235.9	14.4
60°-70°	109.8	6.7
70°-80°	27.3	1.7
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	633.1	38.6
0°-40°	964.7	58.8
0°-60°	1502.8	91.6
0°-90°	1640.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1640.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	917	
5°	911	86
15°	824	231
25°	691	316
35°	527	332
45°	388	302
55°	268	236
65°	108	110
75°	24	27
85°	0	1
90°	0	



TEST NUMBER: P210335

CATALOG NUMBER: PR8R15D010 - PR8M12MDMB - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	917.2
2.5°	912.8
5°	910.6
7.5°	899.5
10°	876.7
12.5°	850.2
15°	824.4
17.5°	792.0
20°	756.7
22.5°	723.6
25°	691.2
27.5°	652.2
30°	610.2
32.5°	567.5
35°	527.0
37.5°	493.2
40°	460.1
42.5°	424.7
45°	387.9
47.5°	358.5
50°	333.5
52.5°	305.5
55°	267.9
57.5°	226.0
60°	182.6
62.5°	141.3
65°	107.5
67.5°	78.0
70°	55.2
72.5°	37.5
75°	23.6
77.5°	13.2
80°	4.4
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)