

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303386

Luminaire Tested: **PR6FS12D010 PR6M12WD9FSMW 1500Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-4)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12WD9FSMW 1500Lm3000K
Description: PR6 WIDE LENS WITH, MATTE WHITE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1315.9 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.33 / 1.33 / 1.28
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 13.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303386

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSMW 1500Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P303386

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSMW 1500Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68
4	88	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60
5	82	71	63	57	80	70	63	57	68	61	57	66	60	56	64	59	55	54
6	76	65	57	51	75	64	56	51	62	55	51	61	55	50	59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43
8	67	54	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	35
10	59	47	39	35	58	46	39	34	45	39	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39275
5°	40185
10°	41497
15°	42484
20°	43045
25°	43241
30°	42737
35°	40077
40°	35199
45°	28777
50°	22410
55°	17517
60°	13896
65°	11099
70°	8813
75°	7108
80°	5786
85°	3818



TEST NUMBER: P303386

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSMW 1500Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.0	4.5
10°-20°	177.5	13.5
20°-30°	276.2	21.0
30°-40°	311.4	23.7
40°-50°	241.5	18.3
50°-60°	140.3	10.7
60°-70°	72.7	5.5
70°-80°	30.7	2.3
80°-90°	6.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	512.7	39.0
0°-40°	824.1	62.6
0°-60°	1205.8	91.6
0°-90°	1315.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1315.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	602	
5°	614	59
15°	629	178
25°	601	276
35°	503	311
45°	312	241
55°	154	140
65°	72	73
75°	28	31
85°	5	7
90°	0	



TEST NUMBER: P303386

CATALOG NUMBER: PR6FS12D010 PR6M12WD9FSMW 1500Lm3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	602.0
2.5°	605.9
5°	613.6
7.5°	621.3
10°	626.4
12.5°	629.0
15°	629.0
17.5°	625.1
20°	620.0
22.5°	612.3
25°	600.7
27.5°	586.6
30°	567.3
32.5°	540.4
35°	503.2
37.5°	460.8
40°	413.3
42.5°	364.5
45°	311.9
47.5°	264.4
50°	220.8
52.5°	183.6
55°	154.0
57.5°	128.4
60°	106.5
62.5°	87.3
65°	71.9
67.5°	59.0
70°	46.2
72.5°	37.2
75°	28.2
77.5°	20.5
80°	15.4
82.5°	10.3
85°	5.1
87.5°	1.3
90°	0.0

(END OF REPORT)