

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210349

Luminaire Tested: **PR8R15D010 - PR8M12MDMMS - 3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8R15D010 - PR8M12MDMMS - 3000K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE METALLIC SILVER FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1543.5 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 15
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210349

CATALOG NUMBER: PR8R15D010 - PR8M12MDMMS - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P210349

CATALOG NUMBER: PR8R15D010 - PR8M12MDMMS - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26606
5°	26515
10°	25823
15°	24760
20°	23358
25°	22122
30°	20438
35°	18664
40°	17422
45°	15913
50°	15049
55°	13553
60°	10589
65°	7377
70°	4679
75°	2645
80°	746
85°	0



TEST NUMBER: P210349

CATALOG NUMBER: PR8R15D010 - PR8M12MDMMS - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.8	5.2
10°-20°	217.3	14.1
20°-30°	297.5	19.3
30°-40°	311.9	20.2
40°-50°	284.3	18.4
50°-60°	221.9	14.4
60°-70°	103.3	6.7
70°-80°	25.7	1.7
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.6	38.6
0°-40°	907.5	58.8
0°-60°	1413.7	91.6
0°-90°	1543.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1543.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	863	
5°	857	81
15°	776	217
25°	650	298
35°	496	312
45°	365	284
55°	252	222
65°	101	103
75°	22	26
85°	0	1
90°	0	



TEST NUMBER: P210349

CATALOG NUMBER: PR8R15D010 - PR8M12MDMMS - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	862.8
2.5°	858.6
5°	856.6
7.5°	846.2
10°	824.7
12.5°	799.8
15°	775.6
17.5°	745.1
20°	711.8
22.5°	680.7
25°	650.2
27.5°	613.5
30°	574.0
32.5°	533.9
35°	495.8
37.5°	463.9
40°	432.8
42.5°	399.5
45°	364.9
47.5°	337.2
50°	313.7
52.5°	287.4
55°	252.1
57.5°	212.6
60°	171.7
62.5°	133.0
65°	101.1
67.5°	73.4
70°	51.9
72.5°	35.3
75°	22.2
77.5°	12.5
80°	4.2
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)