

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303444

Luminaire Tested: **PR6FS12D010 PR6M12WD8FSBZ 1500Lm3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303444
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-6)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12WD8FSBZ 1500Lm3500K
Description: PR6 WIDE LENS WITH, BRONZE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1522.5 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.26
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303444

CATALOG NUMBER: PR6FS12D010 PR6M12WD8FSBZ 1500Lm3500K

Luminous Intensity Polar Plot





TEST NUMBER: P303444

CATALOG NUMBER: PR6FS12D010 PR6M12WD8FSBZ 1500Lm3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85		90	86	83		87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75		82	77	74		79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66		75	70	66		73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		67	62	58	56
6	78	67	59	54	76	66	59	53	64	58	53		63	57	53		61	56	52	50
7	73	61	54	48	71	61	53	48	59	53	48		58	52	48		56	51	47	46
8	68	56	49	44	67	56	49	44	55	48	43		53	48	43		52	47	43	41
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36		46	40	36		45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49244
5°	50316
10°	51792
15°	52919
20°	53577
25°	53722
30°	52658
35°	48949
40°	42421
45°	33649
50°	25019
55°	18438
60°	13440
65°	9123
70°	5799
75°	2546
80°	639
85°	0



TEST NUMBER: P303444

CATALOG NUMBER: PR6FS12D010 PR6M12WD8FSBZ 1500Lm3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	4.8
10°-20°	221.4	14.5
20°-30°	342.6	22.5
30°-40°	380.0	25.0
40°-50°	281.9	18.5
50°-60°	148.2	9.7
60°-70°	61.4	4.0
70°-80°	13.1	0.9
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	637.7	41.9
0°-40°	1017.8	66.8
0°-60°	1447.8	95.1
0°-90°	1522.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1522.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	755	
5°	768	74
15°	784	221
25°	746	343
35°	615	380
45°	365	282
55°	162	148
65°	59	61
75°	10	13
85°	0	0
90°	0	



TEST NUMBER: P303444

CATALOG NUMBER: PR6FS12D010 PR6M12WD8FSBZ 1500Lm3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	754.8
2.5°	759.8
5°	768.3
7.5°	776.7
10°	781.8
12.5°	785.2
15°	783.5
17.5°	780.1
20°	771.7
22.5°	761.5
25°	746.3
27.5°	726.1
30°	699.0
32.5°	663.6
35°	614.6
37.5°	558.9
40°	498.1
42.5°	430.6
45°	364.7
47.5°	302.2
50°	246.5
52.5°	199.2
55°	162.1
57.5°	130.0
60°	103.0
62.5°	79.4
65°	59.1
67.5°	43.9
70°	30.4
72.5°	20.3
75°	10.1
77.5°	3.4
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)