

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210319

Luminaire Tested: **PR8R15D010 - PR8M12MDMW - 3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210319  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8R15D010 - PR8M12MDMW - 3000K  
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE WHITE FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1596.9 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 15  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210319

CATALOG NUMBER: PR8R15D010 - PR8M12MDMW - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P210319

CATALOG NUMBER: PR8R15D010 - PR8M12MDMW - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63		72	67	62		70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27528
5°	27432
10°	26719
15°	25616
20°	24168
25°	22888
30°	21147
35°	19311
40°	18026
45°	16467
50°	15567
55°	14021
60°	10959
65°	7632
70°	4842
75°	2728
80°	764
85°	0



TEST NUMBER: P210319

CATALOG NUMBER: PR8R15D010 - PR8M12MDMW - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.6	5.2
10°-20°	224.8	14.1
20°-30°	307.9	19.3
30°-40°	322.7	20.2
40°-50°	294.1	18.4
50°-60°	229.5	14.4
60°-70°	106.9	6.7
70°-80°	26.6	1.7
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	616.2	38.6
0°-40°	939.0	58.8
0°-60°	1462.6	91.6
0°-90°	1596.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1596.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	893	
5°	886	84
15°	802	225
25°	673	308
35°	513	323
45°	378	294
55°	261	230
65°	105	107
75°	23	27
85°	0	1
90°	0	



TEST NUMBER: P210319

CATALOG NUMBER: PR8R15D010 - PR8M12MDMW - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	892.7
2.5°	888.4
5°	886.2
7.5°	875.5
10°	853.3
12.5°	827.5
15°	802.4
17.5°	770.9
20°	736.5
22.5°	704.3
25°	672.7
27.5°	634.8
30°	593.9
32.5°	552.4
35°	513.0
37.5°	480.0
40°	447.8
42.5°	413.4
45°	377.6
47.5°	348.9
50°	324.5
52.5°	297.3
55°	260.8
57.5°	219.9
60°	177.7
62.5°	137.6
65°	104.6
67.5°	75.9
70°	53.7
72.5°	36.5
75°	22.9
77.5°	12.9
80°	4.3
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)