

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210379

Luminaire Tested: **PR8R15D010 - PR8M12WDMB - 3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210379  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8R15D010 - PR8M12WDMB - 3000K  
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE BLACK FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1443.0 lumens  
Efficiency: N/A  
Efficacy: 96.2 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 15  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210379

CATALOG NUMBER: PR8R15D010 - PR8M12WDMB - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P210379

CATALOG NUMBER: PR8R15D010 - PR8M12WDMB - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	17509
5°	17802
10°	18017
15°	18350
20°	18738
25°	18907
30°	18879
35°	18833
40°	18179
45°	16646
50°	13907
55°	11564
60°	9720
65°	8026
70°	6906
75°	5421
80°	3747
85°	3927



TEST NUMBER: P210379

CATALOG NUMBER: PR8R15D010 - PR8M12WDMB - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.8	3.8
10°-20°	162.7	11.3
20°-30°	255.4	17.7
30°-40°	311.4	21.6
40°-50°	291.0	20.2
50°-60°	194.1	13.5
60°-70°	111.7	7.7
70°-80°	51.5	3.6
80°-90°	10.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	472.9	32.8
0°-40°	784.2	54.3
0°-60°	1269.4	88.0
0°-90°	1443.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1443.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	568	
5°	575	55
15°	575	163
25°	556	255
35°	500	311
45°	382	291
55°	215	194
65°	110	112
75°	46	51
85°	11	10
90°	0	



TEST NUMBER: P210379

CATALOG NUMBER: PR8R15D010 - PR8M12WDMB - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	567.8
2.5°	568.6
5°	575.1
7.5°	574.5
10°	575.4
12.5°	574.2
15°	574.8
17.5°	573.6
20°	571.0
22.5°	561.6
25°	555.7
27.5°	544.0
30°	530.2
32.5°	516.4
35°	500.3
37.5°	480.9
40°	451.6
42.5°	419.6
45°	381.7
47.5°	339.8
50°	289.9
52.5°	247.6
55°	215.1
57.5°	184.0
60°	157.6
62.5°	134.7
65°	110.0
67.5°	90.4
70°	76.6
72.5°	65.1
75°	45.5
77.5°	36.1
80°	21.1
82.5°	13.5
85°	11.1
87.5°	3.2
90°	0.0

(END OF REPORT)