

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210394

Luminaire Tested: **PR8R15D010 - PR8M12WDMMS - 3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210394  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8R15D010 - PR8M12WDMMS - 3000K  
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE METALLIC SILVER FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1529.1 lumens  
Efficiency: N/A  
Efficacy: 101.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 15  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210394

CATALOG NUMBER: PR8R15D010 - PR8M12WDMMS - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P210394

CATALOG NUMBER: PR8R15D010 - PR8M12WDMMS - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18551
5°	18863
10°	19091
15°	19445
20°	19857
25°	20037
30°	20004
35°	19955
40°	19262
45°	17640
50°	14737
55°	12252
60°	10299
65°	8508
70°	7321
75°	5743
80°	3978
85°	4175



TEST NUMBER: P210394

CATALOG NUMBER: PR8R15D010 - PR8M12WDMMS - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.1	3.8
10°-20°	172.4	11.3
20°-30°	270.7	17.7
30°-40°	329.9	21.6
40°-50°	308.4	20.2
50°-60°	205.7	13.5
60°-70°	118.4	7.7
70°-80°	54.6	3.6
80°-90°	11.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.1	32.8
0°-40°	831.0	54.3
0°-60°	1345.1	88.0
0°-90°	1529.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1529.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	602	
5°	609	58
15°	609	172
25°	589	271
35°	530	330
45°	404	308
55°	228	206
65°	117	118
75°	48	55
85°	12	11
90°	0	



TEST NUMBER: P210394

CATALOG NUMBER: PR8R15D010 - PR8M12WDMMS - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	601.6
2.5°	602.6
5°	609.4
7.5°	608.8
10°	609.7
12.5°	608.5
15°	609.1
17.5°	607.9
20°	605.1
22.5°	595.1
25°	588.9
27.5°	576.5
30°	561.8
32.5°	547.2
35°	530.1
37.5°	509.6
40°	478.5
42.5°	444.6
45°	404.5
47.5°	360.1
50°	307.2
52.5°	262.4
55°	227.9
57.5°	195.0
60°	167.0
62.5°	142.7
65°	116.6
67.5°	95.8
70°	81.2
72.5°	69.0
75°	48.2
77.5°	38.2
80°	22.4
82.5°	14.3
85°	11.8
87.5°	3.4
90°	0.0

(END OF REPORT)