

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303422

Luminaire Tested: **PR6FS24D010 PR6M24WD9FSMMS 2000Lm3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-5)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS24D010 PR6M24WD9FSMMS 2000Lm3000K
Description: PR6 WIDE LENS WITH, MATTE METALLIC SILVER FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1924.1 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.33 / 1.33 / 1.27
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303422

CATALOG NUMBER: PR6FS24D010 PR6M24WD9FSMMS 2000Lm3000K

Luminous Intensity Polar Plot





TEST NUMBER: P303422

CATALOG NUMBER: PR6FS24D010 PR6M24WD9FSMMS 2000Lm3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	85	89	86	83	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	77	73	78	75	72	70
4	89	79	72	67	87	78	71	66	76	70	65	74	69	65	72	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55
6	77	66	58	53	76	65	58	52	63	57	52	62	56	52	60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60015
5°	61292
10°	63200
15°	64705
20°	65540
25°	65643
30°	64922
35°	60657
40°	53084
45°	43087
50°	32753
55°	24614
60°	18567
65°	13307
70°	9175
75°	5041
80°	2254
85°	1497



TEST NUMBER: P303422

CATALOG NUMBER: PR6FS24D010 PR6M24WD9FSMMS 2000Lm3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.9	4.7
10°-20°	270.3	14.1
20°-30°	419.5	21.8
30°-40°	470.9	24.5
40°-50°	360.4	18.7
50°-60°	198.0	10.3
60°-70°	88.7	4.6
70°-80°	23.9	1.2
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	779.7	40.5
0°-40°	1250.6	65.0
0°-60°	1809.0	94.0
0°-90°	1924.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1924.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	920	
5°	936	90
15°	958	270
25°	912	419
35°	762	471
45°	467	360
55°	216	198
65°	86	89
75°	20	24
85°	2	2
90°	0	



TEST NUMBER: P303422

CATALOG NUMBER: PR6FS24D010 PR6M24WD9FSMMS 2000Lm3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	919.9
2.5°	925.9
5°	935.9
7.5°	946.0
10°	954.0
12.5°	958.0
15°	958.0
17.5°	952.0
20°	944.0
22.5°	929.9
25°	911.9
27.5°	889.8
30°	861.8
32.5°	817.7
35°	761.6
37.5°	695.4
40°	623.3
42.5°	547.1
45°	467.0
47.5°	390.8
50°	322.7
52.5°	264.5
55°	216.4
57.5°	176.4
60°	142.3
62.5°	112.2
65°	86.2
67.5°	66.1
70°	48.1
72.5°	32.1
75°	20.0
77.5°	12.0
80°	6.0
82.5°	4.0
85°	2.0
87.5°	0.0
90°	0.0

(END OF REPORT)